

6 ft IEEE-1394 Firewire Cable 9-6 M/M

StarTech ID: 1394_96_6



This 6ft IEEE 1394b FireWire 800 Cable provides one FireWire 9-pin and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 800Mbps, FireWire 800 (IEEE 1394b) technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a dv camcorder to a computer, etc.).

This high quality FireWire 800 (9 to 6-pin) cable compatible with all 1394a & 1394b PC FireWire (400/800), Apple FireWire, and Sony iLink devices and is backed by StarTech.com's Lifetime Warranty.

Applications

- Ideal for Mass storage, Digital Video (DV), Digital Audio, Digital Cameras, Printers, Scanners, Home entertainment and other Networking products
- Connect multiple FireWire devices together

Features

- Fast data transfer rate of up to 800 Mbits/sec
- Hot Pluggable feature allows swapping of live devices without turning off your computer
- Compliant with 1394a & 1394b standards
- Compatible with all 1394a & 1394b PC FireWire, Apple FireWire, and Sony iLink devices
- Supports a daisy-chain of up to 63 fireWire devices
- Highest quality shielding protects from EMI (electromagnetic interference) noise
- Twisted Pair Construction

Technical Specifications

Warranty	Lifetime
Industry Standards	IEEE 1394a, 1394b
Connector A	1 - Firewire 800 (9 pin; IEEE 1394b) Male
Connector B	1 - Firewire 400 (6 pin; IEEE 1394a) Male
Maximum Cable Length	14 ft [4.3 m]
Color	Black
Cable Length	6 ft [1.8 m]
Product Weight	0.3 lb [0.1 kg]
Shipping (Package) Weight	0.3 lb [0.1 kg]
Included in Package	1 - 6 ft IEEE-1394 Firewire Cable 9-6 M/M

Certifications, Reports and Compatibility

