

10 ft 1394b Firewire 800 Cable 9-9 M/M

StarTech ID: 1394_99_10



This 10ft 9-pin 1394b Firewire Cable will keep your high-bandwidth video or graphic applications moving data at up to 800 Mbps - enough for demanding high-speed digital storage and serious video capture.

StarTech.com FireWire 800 cables come with the highest quality shielding to protect your high speed data connections, and are backed by our lifetime warranty.

Applications

- Ideal for Mass storage, Digital Video (DV), Digital Audio, Digital Cameras, Printers, Scanners, Home entertainment and other Networking products
- Connect multiple FireWire 800(1394b) compliant devices together

Features

- Fast data transfer rate of up to 800 Mbits/sec
- Hot Pluggable feature allows swapping of live devices without turning off your computer
- Compliant with FireWire800 and 1394b standards
- Compatible with all 1394b PC FireWire, Apple FireWire, and Sony iLink devices
- Supports a daisy-chain of up to 63 fireWire devices
- 9-pin cable draws power from FireWire bus
- Highest quality shielding protects from EMI (electromagnetic interference) noise
- Twisted Pair Construction

Technical Specifications

Warranty	Lifetime
Industry Standards	FireWire 800 & 1394b
Connector A	1 - Firewire 800 (9 pin; IEEE 1394b) Male
Connector B	1 - Firewire 800 (9 pin; IEEE 1394b) Male
Maximum Cable Length	14 ft [4.3 m]
Color	Black
Product Length	10 ft [3 m]
Shipping (Package) Weight	0.6 lb [0.3 kg]
Included in Package	1 - 10 ft 1394b Firewire 800 Cable 9-9 M/M

Certifications, Reports and Compatibility

