

1U 15" Rackmount LCD Console w/ Rear Mount KVM Switch Module

StarTech ID: 1UCABCONS



This 1U Rackmount LCD KVM Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet storage space - a space efficient-solution that provides total KVM control right from a server rack.

The KVM Console combines a 15in TFT-LCD monitor, full 105-key keyboard and touchpad together into a durable, compactable design. When the console is not in use, it's as simple as folding the display and keyboard/mouse up (like a laptop computer) and sliding it back into the server rack on the sturdy mounting rails (included).

A highly scalable solution, the LCD console features a modular design that lets you install a multi-port KVM switch directly into the back of the console, allowing you to control multiple servers from a single point while only taking up 1U of rack space.

To simplify maintenance and ensure long-lasting performance, the console keyboard and touch pad are both replaceable - allowing you to swap out components as needed, without replacing the entire console.

Applications

- Managing cabinet mounted servers
- Improving the internal space efficiency of existing cabinets
- Centralized control of dozens of PCs and servers if used with optional KVM modules.

Features

- Modular design allows optional 8 or 16 port KVM switch modules to be integrated into the unit.
- 15 Inch TFT LCD Display
- Supports resolution up to 1024x768 pixels
- Standard 19" 1U rack drawer
- Full 105 key low profile keyboard
- Extendable rails can be adjusted between 67.5 cm (26.63 in) and 80.5 cm (31.69 in)
- Quick and easy installation

Technical Specifications

Warranty	2 Years
Audio	No
KVM Ports	1
PC Interface	PS/2
Multi-Monitor	No
Rack-Mountable	Yes
Daisy-Chain	Yes
DVI Support	No
IP Control	No
Maximum Number of Users	1
MTBF	384,893 Hours
General Specifications	1024 x 768 @60/70/75Hz
General Specifications	105 Key, PS/2
General Specifications	15.1 inches TFT
General Specifications	16.7M (8 bits)
General Specifications	30 in. (minimum)
General Specifications	FCC (Part 15)
General Specifications	OFF mode <= 1W
General Specifications	ON mode = 23.2W
General Specifications	OSD control (auto saving)
General Specifications	PS/2
General Specifications	RGB analog, H/V separate
General Specifications	STANDBY mode <= 1W
General Specifications	SUSPEND mode <= 1W
General Specifications	VESA DDC 1/2B
General Specifications	VESA DPMS compliant
Enclosure Type	Steel
Product Length	18.9 in [48 cm]
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Input Current	1.8A
Output Voltage	12 DC
Output Current	4A
Center Tip Polarity	Positive

Plug Type	M
Operating Temperature	05/22/2012eg;C to 505/22/2012eg;C (325/22/2012eg;F to 1225/22/2012eg;F)
Storage Temperature	-205/22/2012eg;C to 605/22/2012eg;C (-45/22/2012eg;F to 1405/22/2012eg;F)
System and Cable Requirements	Extendable rails can be adjusted between 67.5 cm (26.63 in) and 80.5 cm (36.63 in)
Shipping (Package) Weight	32.7 lb [14.8 kg]
Included in Package	1 - 1U Cabinet Command Console
Included in Package	1 - PC/KVM Console
Included in Package	1 - Rear Bracket and Extension Kit
Included in Package	1 - Bag of Rackmount Screws
Included in Package	1 - Power Cord
Included in Package	1 - Power Adapter
Included in Package	1 - Manual
Connector Type(s)	1 - VGA (15 pin; High Density D-Sub) Female
Connector Type(s)	2 - PS/2 (6 pin; Mini-DIN) Female

Certifications, Reports and Compatibility

