

## 1U 17" Rack Mount LCD Console w/ Rear Mount KVM Switch Module

StarTech ID: 1UCABCONS17



This 1U Rackmount LCD KVM Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet storage space - a space efficient-solution that provides total KVM control right from a server rack.

The KVM Console combines a 17in TFT-LCD monitor, full 105-key keyboard and touchpad together into a durable, compactable design. When the console is not in use, it's as simple as folding the display and keyboard/mouse up (like a laptop computer) and sliding it back into the server rack on the sturdy mounting rails (included).

A highly scalable solution, the LCD console features a modular design that lets you install a multi-port KVM switch directly into the back of the console, allowing you to control multiple servers from a single point while only taking up 1U of rack space.

To simplify maintenance and ensure long-lasting performance, the console keyboard and touch pad are both replaceable - allowing you to swap out components as needed, without replacing the entire console.

## Features

- A compact and efficient way to control multiple computers in a 19" by 36" deep Rack Cabinet.
- Adjustable mounting brackets to fit any cabinet
- Comfortable laptop design with integrated keyboard and touchpad mouse
- Drawer locks firmly into position firmly when in use
- High resolution 17" Active Matrix Color TFT LCD monitor, displays up to 1280 x 1024 pixels
- Optional 8 or 16 port KVM switch modules lets users controls up to 16 computers directly, and up to 136 computers in total
- Quick and easy installation
- Standard 19" 1U rack drawer

## Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Connector Types: 2 - 6 DIN Female
- Connector Types: 1 - High Density DB15 Female
- Enclosure Type: Steel
- Product Height: 15 in [381 mm]
- Audio Support: No
- Cascadable: Yes
- Dual Display Support: No
- DVI Support: No
- Supported Platforms: PS/2
- KVM IP Control: No
- Number of KVM Ports: 1
- Rack-Mountable: Yes
- KVM TFT: 17
- Product Length: 20.67 in [525 mm]
- Maximum Number of Users: 1
- Operating Temperature: 0 to +50°C
- Carton Quantity: 1
- Storage Temperature: -20 to +60°C
- Shipping (Package) Weight: 41.06 lb [18.58 kg]

- Product Weight: 22.43 lb [10.15 kg]
- Product Width: 19 in [482.6 mm]
- LCD Size: 17 inches TFT
- Display Colors: 16.7M (8 bits)
- User Control: OSD control (auto saving)
- Input Signal: RGB analog, H/V separate
- Plug and Play VESA: VESA DDC 1/2B
- Keyboard: 105 Key, PS/2
- Mouse Touch Pad: PS/2
- Power Management: VESA DPMS compliant
- ON mode =: 23.2W
- STANDBY mode <=: 1W
- SUSPEND mode <=: 1W
- OFF mode <=: 1W
- Rack/Cabinet Depth Requirement: 30 in. (minimum)
- Power: DV 12V - 4A - Center Positive
- Contrast Ratio: 500:1
- MTBF: 360,562 hours

