

1U 17" Rackmount LCD Console w/ Rear Mount KVM Switch Module

StarTech ID: 1UCABCONS17



This 1U Rackmount LCD KVM Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet storage space - a space efficient-solution that provides total KVM control right from a server rack.

The KVM Console combines a 17in TFT-LCD monitor, full 105-key keyboard and touchpad together into a durable, compactable design. When the console is not in use, it's as simple as folding the display and keyboard/mouse up (like a laptop computer) and sliding it back into the server rack on the sturdy mounting rails (included).

A highly scalable solution, the LCD console features a modular design that lets you install a multi-port KVM switch directly into the back of the console, allowing you to control multiple servers from a single point while only taking up 1U of rack space.

To simplify maintenance and ensure long-lasting performance, the console keyboard and touch pad are both replaceable - allowing you to swap out components as needed, without replacing the entire console.

Features

- A compact and efficient way to control multiple computers in a 19" by 36" deep Rack Cabinet.
- Comfortable laptop design with integrated keyboard and touchpad mouse
- Optional 8 or 16 port KVM switch modules lets users controls up to 16 computers directly, and up to 136 computers in total
- High resolution 17" Active Matrix Color TFT LCD monitor, displays up to 1280 x 1024 pixels
- Adjustable mounting brackets to fit any cabinet
- Standard 19" 1U rack drawer
- Drawer locks firmly into position firmly when in use
- Quick and easy installation

Technical Specifications

Warranty	2 Years
Key Lock	No
Audio	No
Display Size	17in
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	PS/2
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	Yes
Industry Standards	VESA DDC 1/2B, VESA DPMS compliant
Daisy-Chain	Yes
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Brightness	350 cd/m ²
Contrast Ratio	1000:1
Pixel Pitch Support	0.264 x 0.264 mm
Response Time	5ms
Viewing Angle	170° (H), 160° (V)
DVI Support	No
IP Control	No
Maximum Analog Resolutions	1280 x 1024
Aspect Ratio	Standard (4:3)
Color Depth	8-bit, 16.7M colors
Maximum Number of Users	1
Port Selection Support	Push Button and OSD (On Screen Display)
MTBF	360,562 Hours
Maximum Mounting Depth	
Minimum Mounting Depth	30.1 in [765 mm]
Product Height	15 in [381 mm]
Product Length	20.7 in [525 mm]
Product Weight	22.4 lb [10.2 kg]
Product Width	19 in [482.6 mm]
Color	Black

Enclosure Type	Steel
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Input Current	1.8A
Output Voltage	12 DC
Output Current	4A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption	26.5W
Operating Temperature	05/8/2012eg;C to 505/8/2012eg;C (325/8/2012eg;F to 1225/8/2012eg;F)
Storage Temperature	-205/8/2012eg;C to 605/8/2012eg;C (-45/8/2012eg;F to 1405/8/2012eg;F)
Note	Power consumption for Standby, Suspend and Off modes is <= 1W
Shipping (Package) Weight	41.1 lb [18.6 kg]

Certifications, Reports and Compatibility

