

1U 19" Rack Mount LCD Console w/ Rear Mount KVM Switch Module

StarTech ID: 1UCABCONS19



This 1U Rackmount LCD KVM Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet storage space - a space efficient-solution that provides total KVM control right from a server rack.

The KVM Console combines a 19in TFT-LCD monitor, full 105-key keyboard and touchpad together into a durable, compactable design. When the console is not in use, it's as simple as folding the display and keyboard/mouse up (like a laptop computer) and sliding it back into the server rack on the sturdy mounting rails (included).

A highly scalable solution, the LCD console features a modular design that lets you install a multi-port KVM switch directly into the back of the console, allowing you to control multiple servers from a single point while only taking up 1U of rack space.

To simplify maintenance and ensure long-lasting performance, the console keyboard and touch pad are both replaceable - allowing you to swap out components as needed, without replacing the entire console.

Applications and Solutions

- Centralized control of dozens of PCs and servers if used with optional KVM modules.
- Improving the internal space efficiency of existing cabinets
- Managing cabinet-mounted servers

Features

- Ergonomic hand rest design
- Flip-open 19" TFT LCD panel supports 1280 x 1024@60/70/75Hz resolution
- For rack cabinet with depth from 20" (50cm) and up (with appropriate Rear bracket & extension kit)
- Full 105 key, low-profile, sturdy keyboard built-in
- Locking mechanism locks the drawer when pulled out, pushed in or folded down
- Modular design
- Quick and easy installation
- Standard 19" 1U rack drawer
- Standard connectors for PC connection
- Supports replaceable keyboard, mouse and module selection

Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Audio Support: No
- Cascadable: Yes
- Dual Display Support: No
- DVI Support: No
- Supported Platforms: PS/2
- KVM IP Control: No
- Rack-Mountable: Yes
- KVM TFT: 19
- Maximum Analog Resolutions: 1280 x 1024 pixels
- Operating Temperature: 0 to +50
- Carton Quantity: 1
- Storage Temperature: -20 to +60
- Shipping (Package) Weight: 45.53 lb [20.6 kg]
- Screen Size/Type: 19" TFT LCD
- Keyboard/Mouse: 105-key keyboard + integrated touchpad (with scroll)
- Form Factor: 1U (when closed)
- Power Management: VESA DPMS compliant
- Input Signal: RGB Analog, H/V Separate
- MTBF: 360,562 hours

