

## 1U 19" Rackmount LCD Console w/ Rear Mount KVM Switch Module

StarTech ID: 1UCABCONS19



This 1U Rackmount LCD KVM Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet storage space - a space efficient-solution that provides total KVM control right from a server rack.

The KVM Console combines a 19in TFT-LCD monitor, full 105-key keyboard and touchpad together into a durable, compactable design. When the console is not in use, it's as simple as folding the display and keyboard/mouse up (like a laptop computer) and sliding it back into the server rack on the sturdy mounting rails (included).

A highly scalable solution, the LCD console features a modular design that lets you install a multi-port KVM switch directly into the back of the console, allowing you to control multiple servers from a single point while only taking up 1U of rack space.

To simplify maintenance and ensure long-lasting performance, the console keyboard and touch pad are both replaceable - allowing you to swap out components as needed, without replacing the entire console.

### Applications

- Managing cabinet-mounted servers
- Improving the internal space efficiency of existing cabinets
- Centralized control of dozens of PCs and servers if used with optional KVM modules.

## Features

- Flip-open 19" TFT LCD panel supports 1280 x 1024@60/70/75Hz resolution
- Standard 19" 1U rack drawer
- Modular design
- Full 105 key, low-profile, sturdy keyboard built-in
- Standard connectors for PC connection
- Locking mechanism locks the drawer when pulled out, pushed in or folded down
- Supports replaceable keyboard, mouse and module selection
- Ergonomic hand rest design
- For rack cabinet with depth from 20" (50cm) and up (with appropriate Rear bracket & extension kit)
- Quick and easy installation

## Technical Specifications

Warranty	2 Years
Key Lock	No
Audio	No
Display Size	19in
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	PS/2
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	Yes
Industry Standards	VESA DPMS compliant
Daisy-Chain	Yes
Brightness	300 cd/m <sup>2</sup>
Contrast Ratio	2000:1
Pixel Pitch Support	0.294 x 0.294 mm
Response Time	8ms
Viewing Angle	178° (H), 178° (V)
DVI Support	No
IP Control	No
Maximum Analog Resolutions	1280 x 1024 pixels
Aspect Ratio	Standard (4:3)
Color Depth	8-bit, 16.7M colors
MTBF	360,562 Hours
Maximum Mounting Depth	
Minimum Mounting Depth	
Product Height	
Product Length	
Product Weight	
Product Width	
Color	Black
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Input Current	1.8A
Output Voltage	12 DC

Output Current	4A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption	28W
Operating Temperature	0 to +50
Storage Temperature	-20 to +60
Shipping (Package) Weight	45.5 lb [20.6 kg]

**Certifications, Reports and Compatibility**

