

Assembly Instructions

2POSTRACK

StarTech.com



Thank you for purchasing a StarTech.com 2POSTRACK. Ideal for rackmount equipment, KVM switches, or cabinet consoles, this open server rack provides fast and easy access to all your installed rackmount equipment. With total ventilation and an unobstructed airflow, this rack keeps your equipment at room temperature and is suitable for equipment where security at the rack level is not required.

Step 1



Place the top (part with the DuraRak symbol), bottom, and each side post of the 2POSTRACK on the ground for positioning of alignment.



Step 2

When the panels are aligned, the holes should match up with each other allowing you to use the Allen Key to fasten each corner with the nuts and bolts provided.

Step 3

Once one side of the 2POSTRACK is fastened please flip the rack over and follow the instructions in **Step 2**.

Step 4



Attach the casters, which are included with the packaging, to the legs of the 2POSTRACK. Use a Phillips screwdriver and screws to mount the casters to the legs of the unit.

Step 5

Mount the legs to the base of the rack and attach them with the screws and nuts. Use the Allen key to fasten the nuts and screws and stand the rack up.



Step 6

Using the rackmount screws and cage nuts, install your rackmount equipment in the 2POSTRACK.