

3.5in Bay 20-in-1 USB 2.0 Multi Media Memory Card Reader - Black

StarTech ID: 35FCREAD20BK



This 20-in-1 USB 2.0 Media Memory Card Reader can be installed in a 3.5in drive bay or used as a standalone media card reader by simply connecting to an available USB port. The card reader offers full read/write access to popular media/memory card formats - a convenient solution for transferring data from digital media devices such as digital cameras, DV camcorders etc. to a computer without having to connect the digital media device directly to the computer.

The media/memory card reader supports high-speed USB 2.0 transfer rates up to 480Mbps - providing quick, simple access to memory card contents, eliminating lag while trying to transfer important files.

The card reader is a versatile and cost-effective solution that lets you access popular media card formats including CompactFlash (CF I, CF II), IBM MicroDrives, Smart Media, Multi-Media, and Memory Sticks (MS, MS Pro), Secure Digital (SD, SD Mini) etc., allowing you to use a single card reader for all of the different memory cards you use, as opposed to using different memory card readers for each application.

Applications

- Transfer photos from a digital camera memory card to a laptop or desktop
- Transfer music from a computer to a memory card for use in a portable music player

Features

- Designed to install internally or as an external card reader
- Support for CompactFlash (CF type I/II, MicroDrive), SmartMedia (SM), MultiMedia Card (MMC), SecureDigital (SD) and MemoryStick (MS, MSPro, MS Duo, MSProDuo)
- Powered directly from the USB port
- Status and activity LED indicators
- High Speed USB 2.0 host interface with support for transfer rates up to 480 Mbps
- Plug-and-Play and Hot-Swap compatible

Technical Specifications

Warranty	2 Years
Connector Type(s)	1 - IDC (5 pin; Motherboard Header) Female
Connector Type(s)	1 - USB A (4 pin) Male
External Ports	1 - CompactFlash (50 pin) Slot
External Ports	1 - Memory Stick / Memory Stick Pro Slot Female
External Ports	1 - SD / MMC Slot Female
External Ports	1 - SmartMedia Slot Female
External Ports	1 - USB B (4 pin) Female
Maximum Data Transfer Rate	USB 2.0 480Mbps, USB 1.1 12Mbps
Memory Media Type	CF (Compact Flash /II Card)
Memory Media Type	IBM Micro Drive
Memory Media Type	MS Duo, MS Pro Duo, MS Pro-HG Duo
Memory Media Type	MS/MS Pro (Memory Stick/Memory Stick Pro)
Memory Media Type	SD/MMC (Secure Digital/Multimedia Card)
Memory Media Type	SM (SmartMedia)
OS Compatibility	Windows 98SE/ ME/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS X and up
Color	Black
Enclosure Type	Plastic
Product Length	4.4 in [111 mm]
Product Width	3.8 in [9.6 cm]
Product Height	1 in [26.3 mm]
Product Weight	3.5 oz [100 g]
LED Indicators	1 - 4 x Status/Activity LED's for each card socket
LED Indicators	1 - Power LED (red)
Note	The chipset for the 35FCREAD20BK can support up to 1G SD,MMC and MS card
Shipping (Package) Weight	0.5 lb [0.2 kg]
Included in	1 - 20-in-1 Card Reader

Package	
Included in Package	1 - USB Type B to A cable (for standalone use)
Included in Package	1 - USB Type B to Motherboard header cable
Included in Package	1 - Stand (for standalone use)
Included in Package	1 - Four Screws
Included in Package	1 - Four Rubber Pads
Included in Package	1 - Driver CD
Included in Package	1 - User Manual

Certifications, Reports and Compatibility

