

3.5in Front Bay 22-in-1 USB 2.0 Multi Media Memory Card Reader - Black

StarTech ID: 35FCREADBK2



This 3.5-inch Front Bay Mount 22-in-1 Multimedia Card Reader allows for quick and easy access to the most popular flash card formats, from almost any desktop computer with a 3.5-inch bay opening.

With support for Compact Flash (CF type I/II), Secure Digital (SD/miniSD/microSD/SDHC/SDXC), MultiMediaCard (MMC/RS-MMC/HS-MMC/MMCmobile/MMCplus/MMCmicro/HC-MMC), MemoryStick (MS/MS Duo/HS-MS/MS PRO/MS PRO Duo/MS PRO-HG Duo/MS-ROM/M2), and xD Picture cards, this reader is ready to handle the memory cards from virtually any portable device from cameras to music players.

Applications

- Photographers who need to regularly transfer files from their camera memory card to a computer
- Transferring files to and from a variety of portable devices, each using a different memory card format

Features

- Supports CompactFlash type I/II, SD/miniSD/microSD/SDHC/SDXC, MMC/RS-MMC/HS-MMC/MMCmobile/MMCplus/MMCmicro/HC-MMC, MemoryStick (MS/MS Duo/HS-MS/MS PRO/MS PRO Duo/MS PRO-HG Duo/MS-ROM/M2), and xD Picture card
- Front panel USB port for convenient access
- Fits into any external 3.5in drive bay
- High Speed USB 2.0 compliant, with support for data transfer rates up to 480 Mbps
- Powered directly from the USB connection
- Durable metal enclosure
- Power/Activity LED indicator
- Connects internally to a 9-pin USB motherboard header via included cable
- Plug and Play compatible

Technical Specifications

Warranty	2 Years
Chipset ID	ITE - 1336
Connector Type(s)	1 - IDC (10 pin; Motherboard Header) Female
External Ports	1 - CompactFlash (50 pin) Slot
External Ports	1 - Memory Stick / Memory Stick Pro Slot Female
External Ports	1 - Memory Stick Micro (M2) Slot Female
External Ports	1 - MiniSD / MicroSD / MMC Slot Female
External Ports	1 - SD / MMC Slot Female
External Ports	1 - USB A (4 pin) Female
External Ports	1 - xD-Picture Card Slot Female
Memory Media Type	CF (Compact Flash /III Card)
Memory Media Type	HS-MMC, HC-MMC (High Speed/High Capacity Multimedia Card)
Memory Media Type	HS-MS (High Speed Memory Stick)
Memory Media Type	M2 (Memory Stick Micro)
Memory Media Type	Memory Stick
Memory Media Type	Micro-SDHC (Micro Secure Digital High Capacity)
Memory Media Type	Mini-SD, Micro-SD (Mini/Micro Secure Digital)
Memory Media Type	MS Duo, MS Pro Duo, MS Pro-HG Duo
Memory Media Type	Multi Media Card
Memory Media Type	RS-MMC (Reduced Size Multimedia Card)
Memory Media Type	SD/MMC (Secure Digital/Multimedia Card)
Memory Media Type	SDHC (Secure Digital High Capacity)
Memory Media Type	SDXC (Secure Digital eXtended Capacity)
Memory Media Type	xD (Extreme Digital) Picture Card
OS Compatibility	Windows 2000/ XP(32/64-bit)/ Server 2003(32/64-bit)/ Server 2008 R2/ Vista(32/64-bit)/ 7(32/64-bit)/ 8 (32/64-bit) Linux kernel 2.4.x or later
Color	Black
Enclosure Type	Steel and Plastic
Product Length	5.1 in [130 mm]
Product Width	4.1 in [105 mm]
Product Height	1 in [25 mm]
Product Weight	5.8 oz [164 g]
LED Indicators	1 - Power/Activity
Power Adapter Included	Self Powered

Operating Temperature	05/9/2012eg;C to 705/9/2012eg;C (325/9/2012eg;F to 1585/9/2012eg;F)
Storage Temperature	-405/9/2012eg;C to 1255/9/2012eg;C (-405/9/2012eg;F to 2575/9/2012eg;F)
Humidity	15~85%
System and Cable Requirements	Available internal 9-pin USB motherboard header
Shipping (Package) Weight	7.8 oz [220 g]
Included in Package	1 - Card Reader
Included in Package	1 - 9-pin IDC USB cable
Included in Package	1 - Bag of Mounting Screws
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

