

10 ft Cat5e Gray Snagless Crossover RJ45 UTP Cat5e Patch Cable 10ft Patch Cord

StarTech ID: 45CROSS10GR



StarTech.com's 10 ft Gray Cat 5e UTP Snagless Crossover Patch Cable is constructed of only top quality materials (100% Copper core, 24 Gauge Wire, 50 micron Gold Connectors) to ensure optimum durability and is backed by our Lifetime Warranty.

Applications

- Connects workstation to workstation
- Patches from hub to hub

Features

- StarTech Category 5e Patch cables are constructed of top quality components
- The Strain relief prevents the cable from being bent at sharp angles at the connector to minimize the stress at the plug termination point
- Coloured Hoods for departmental colour coding
- StarTech Category 5e patch cables are carefully constructed and tested, to keep the Near End Crosstalk (NEXT) well within acceptable limits
- Clip protector keeps the plug from snagging while routing the cable

Technical Specifications

Warranty	Lifetime
Number of Conductors	4 pair UTP
Fire Rating	CM Rated
Cable Type	Crossover Snag-less
Connector A	1 - RJ-45 Male
Connector B	1 - RJ-45 Male
Cable Rating	CAT5e - 350 MHz
Color	Gray
Wire Gauge	24 AWG
Cable Length	10 ft [3 m]
Product Length	10 ft [3 m]
Shipping (Package) Weight	0.3 lb [0.1 kg]
Included in Package	1 - 10 Ft Gray Cross Wired RJ45 Patch Cable

Certifications, Reports and Compatibility

