

**10 ft Yellow Snagless Cat5e Crossover UTP Patch Cable**

*StarTech ID: 45CROSS10YL*



StarTech.com's 10 ft (Yellow) Cat 5e UTP Snagless Crossover Patch Cable is constructed of only top quality materials (100% Copper core, 24 Gauge Wire, 50 micron Gold Connectors) to ensure optimum durability and is backed by our Lifetime Warranty.

**Applications and Solutions**

- Connects workstation to workstation
- Patches from hub to hub

## Features

- Clip protector keeps the plug from snagging while routing the cable
- Coloured Hoods for departmental colour coding
- StarTech Category 5e patch cables are carefully constructed and tested, to keep the Near End Crosstalk (NEXT) well within acceptable limits
  - StarTech Category 5e Patch cables are constructed of top quality components
  - The Strain relief prevents the cable from being bent at sharp angles at the connector to minimize the stress at the plug termination point

## Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - RJ45 Male
- Connector B: 1 - RJ45 Male
- Color: Yellow
- Product Length: 10 ft [3.05 m]
- Maximum Cable Length: 328 ft [100 m]
- Network Cable Type: Crossover Snag-less
- Carton Quantity: 120
- Shipping (Package) Weight: 0.24 lb [0.11 kg]
- Connectors: RJ45 Male, RJ45 Male
- Length: 10 ft. [3.0m]
- Cable: 24 AWG, 4 pair UTP, CAT-5e tested to 350 MHz, type CM (UL) certified, Category 5e

