

100 ft Black Snagless Cat5e UTP Patch Cable

StarTech ID: 45PATCH100BK



StarTech.com's Cat5e UTP Snagless Patch Cables offer reliable Ethernet connections. This 100 ft cable meets or exceeds all Category 5e specifications and features a durable black jacket that simplifies departmental color coding while providing rugged flexibility for network connections.

To ensure long-lasting performance, our high quality Cat5e UTP Snagless Patch Cables feature a snagless design that protects the RJ45 clip from damage and makes the cables less prone to snagging during installation. The cables also feature PVC molded strain relief that prevents the RJ45 connector termination point from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

StarTech.com's 100 ft Black Cat5e UTP Snagless Patch Cable is constructed of only top quality materials to ensure optimum durability and is backed by our Lifetime Warranty.

Applications and Solutions

- Connects workstation to wall outlet
- Patches from hub to distribution panel

Features

- Clip protector keeps the plug from snagging while routing the cable
- Coloured Hoods for departmental colour coding
- StarTech Category 5e patch cables are carefully constructed and tested, to keep the Near End Crosstalk (NEXT) well within acceptable limits
 - StarTech Category 5e Patch cables are constructed of top quality components
 - The Strain relief prevents the cable from being bent at sharp angles at the connector to minimize the stress at the plug termination point

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - RJ45 Male
- Connector B: 1 - RJ45 Male
- Color: Black
- Product Length: 99.97 ft [30.48 m]
- Maximum Cable Length: 328 ft [100 m]
- Network Cable Type: Snag-less
- Carton Quantity: 20
- Shipping (Package) Weight: 2.36 lb [1.07 kg]
- Connectors: RJ45 Male, RJ45 Male
- Length: 100 ft., 30.4m
- Cable: 24 AWG, 4 pair UTP, CAT-5e tested to 350 MHz, type CM (UL) certified, Category 5e

