

Caster Kit for Open Frame Rack - 4POSTRACK

StarTech ID: 4POSTCASTER



This set of four casters connects to the bottom of our [42U Adjustable 4 Post Open Server Equipment Rack \(4POSTRACKBK\)](#), allowing you to move and adjust the position of your rack/cabinet to suit your needs.

Features

- Max load capacity of 50 kg (110 lbs) per caster, total of 200 kg (440 lbs)
- Includes all hardware required for installation

Technical Specifications

Warranty	Lifetime
Weight Capacity	442 lb [200 kg]
Product Height	3.2 in [82.5 mm]
Shipping (Package) Weight	4 lb [1.8 kg]
Included in Package	4 - Casters
Included in Package	16 - Mounting Screws

Certifications, Reports and Compatibility

