

25U 4 Post Server Open Frame Rack

StarTech ID: 4POSTRACK25



StarTech.com's DuraRak 25U 4 Post Open Frame Rack/Cabinet provides a durable, open air housing for rackmount servers and networking equipment.

The equipment rack/cabinet features heavy gauge mounting rails to ensure a stable installation platform and adjustable posts for flexible installation.

The 25U rack is compliant with EIA-RS-310C standards, offering a universal design that's compatible with equipment from popular manufacturers. Plus, the equipment rack is flat-packed, reducing shipping costs and simplifying handling and assembly.

For even more versatility, StarTech.com offers an optional [4pc Caster Kit](#) (4POSTCASTER) that can be installed on the bottom of the 25U server rack, making it easier to re-position the cabinet/rack as needed for future uses.

The DuraRak 25U 4-Post Open Racks offer a durable housing for valuable equipment, backed by Lifetime Warranty.

Applications and Solutions

- Audio/Video editing room, radio or television studio broadcast rackmount equipment
- Durable storage for rackmount servers, KVM switches, and networking equipment
- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Suitable for rackmount equipment where security at the rack level is not required

Features

- Adjustable mounting rails ensure broad equipment compatibility
- Heavy gauge mounting rails
- Unobstructed ventilation and cable routing

Technical Specifications

- Warranty: 3 Year warranty
- Color: Black
- Carton Quantity: 1
- Shipping (Package) Weight: 93.93 lb [42.5 kg]
- U Height: 25
- Material Thickness: 2 Millimeters
- Weight Capacity: 994.5 lb [450 kg]
- Frame Type: : Steel
- Casters:: Optional
- External Height : 47.75 in [1212.85 mm]
- External Width : 22.48 in [571 mm]
- External Depth : 39.37 in [1000 mm]
- Maximum Mounting Depth:: 31.5 in [800.1 mm]
- Minimum Mounting Depth:: 23.5 in [596.9 mm]
- Product Weight: 86.19 lb [39 kg]

