

## 25U 4 Post Server Open Frame Rack Cabinet

StarTech ID: 4POSTRACK25



StarTech.com's DuraRak 25U 4 Post Open Frame Rack/Cabinet provides a durable, open air housing for rackmount servers and networking equipment.

The equipment rack/cabinet features heavy gauge mounting rails to ensure a stable installation platform and adjustable posts for flexible installation.

The 25U rack is compliant with EIA-RS-310C standards, offering a universal design that's compatible with equipment from popular manufacturers. Plus, the equipment rack is flat-packed, reducing shipping costs and simplifying handling and assembly.

For even more versatility, StarTech.com offers an optional [4pc Caster Kit](#) (4POSTCASTER) that can be installed on the bottom of the 25U server rack, making it easier to re-position the cabinet/rack as needed for future uses.

The DuraRak 25U 4-Post Open Racks offer a durable housing for valuable equipment, backed by Lifetime Warranty.

### Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

## Features

- Adjustable mounting rails ensure broad equipment compatibility
- Heavy gauge mounting rails
- Unobstructed ventilation and cable routing

## Technical Specifications

Warranty	Lifetime
Casters	Optional
U Height	25U
Frame Type	Open Frame
Wallmountable	No
Front Door Type	Open
Fan(s)	No
Weight Capacity	994.5 lb [450 kg]
Color	Black
Internal Width	18.3 in [466 mm]
External Width	22.5 in [571 mm]
External Height	48.2 in [1224 mm]
External Depth	31.5 in [800 mm]
Product Weight	86.2 lb [39 kg]
Maximum Mounting Depth	31.5 in [800.1 mm]
Minimum Mounting Depth	23.5 in [596.9 mm]
Flat Pack	Yes
Shipping (Package) Weight	93.9 lb [42.5 kg]
Included in Package	1 - 25U 4 Post Rack

## Certifications, Reports and Compatibility

