

36U Adjustable 4 Post Server Equipment Open Frame Rack

StarTech ID: 4POSTRACK36



StarTech.com's DuraRak 36U Open 4 Post Rack/Cabinet provides a durable, open air housing for rackmount servers and networking equipment.

The equipment rack/cabinet features heavy gauge mounting rails to ensure a stable installation platform and adjustable posts for flexible installation.

The 36U rack is compliant with EIA-RS-310C standards, offering a universal design that's compatible with equipment from popular manufacturers. Plus, the equipment rack is flat-packed, reducing shipping costs and simplifying handling and assembly.

For even more versatility, StarTech.com offers an optional [4pc Caster Kit](#) (4POSTCASTER) that can be installed on the bottom of the 36U server rack, making it easier to re-position the cabinet/rack as needed for future uses.

StarTech.com also offers the following Open Frame 4-Post Rack/Cabinets:

- [12U Open 4 Post Rack/Cabinet](#)
- [25U Open 4 Post Rack/Cabinet](#)
- [42U Open 4 Post Rack/Cabinet](#)

The DuraRak 36U 4-Post Open Racks offer a durable housing for valuable equipment, backed by Lifetime Warranty.

Applications and Solutions

- Audio/Video editing room, radio or television studio broadcast rackmount equipment
- Durable storage for rackmount servers, KVM switches, and networking equipment
- Great for satellite offices, and retail locations where a small amount of server equipment is setup
- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Suitable for rack mount equipment where security at the rack level is not required

Features

- Adjustable mounting rails ensure broad equipment compatibility
- Heavy gauge mounting rails
- Heavy-duty, pre-drilled base lets you bolt the server rack to the floor when mounting heavy rackmount equipment
- Unobstructed ventilation

Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- U Height: 36
- Weight Capacity: 1000 lb [452.49 kg]
- Frame Type: : Steel
- Casters:: Optional
- External Width : 22.48 in [571 mm]
- Internal Height: 63.13 in [1603.5 mm]
- Internal Width: 17.76 in [451 mm]
- External Height : 67.46 in [1713.5 mm]
- Product Weight: 92.82 lb [42 kg]
- Maximum Mounting Depth:: 35.25 in [895.35 mm]
- Minimum Mounting Depth:: 18.5 in [469.9 mm]
- Industry Standards: EIA RS310-C
- Shipping (Package) Weight: 1659.1 oz [47000 g]
- Carton Quantity: 1

