

45U 3300lb High Capacity 4 Post Open Server Equipment Rack - Flat Pack

StarTech ID: 4POSTRACKHD



This 45U 4 Post Open Frame Server Equipment Rack offers a solid, reliable solution for mounting servers, UPSs, and other heavy rack-mountable equipment.

Supporting a total weight capacity of up to 3300lbs (without casters) - nearly double the capacity of competitive models, this full size (45U) rack features an open frame design with heavy gauge mounting rails that ensure exceptional structural stability.

Built to meet EIA standards for 19in racks, the 4-post open frame rack is compatible with equipment and accessories from most popular manufacturers.

A durable, cost-effective server room storage solution, StarTech.com's DuraRak 45U 4 Post Open Frame Server Equipment Rack is backed by 2-year warranty.

Applications and Solutions

- Ideal mounting option for heavy equipment like UPSs and storage servers in environments such as server farms, factory and other industrial applications

- Equipped to support servers, KVM switches, networking equipment and cabinet consoles
- Suitable for rack mount equipment where security at the rack level is not required

Features

- Easily route, manage and access your equipment cables without any obstruction
- Fixed heavy duty rails with front/rear and side mounting options
- Flat-pack packaging for easier handling and reduced shipping expenses. Assembles in minutes.
- Heavy-duty design supporting a maximum weight load of 3300 lb. (1493.21 kg.)with Pre-drilled holes allowing the rack to be secured directly to the floor for additional stability
 - Meets ANSI/EIA RS-310-D standards
 - Open frame design with heavy gauge mounting rails provides exceptional structural stability
 - Package includes all necessary hardware to assemble the rack with a **free** pack of 50 cage screws and nuts for immediate hardware installation
 - Provides ample ventilation and unobstructed air flow keeping your rack mount equipment at room temperature

Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Carton Quantity: 1
- U Height: 45
- Shipping (Package) Weight: 125.09 lb [56.6 kg]
- Weight Capacity: 3300 lb [1493.21 kg]
- Frame Type: : Steel
- External Height : 84.05 in [2135 mm]
- External Width : 23.98 in [609 mm]
- External Depth : 36 in [914.4 mm]
- Internal Height: 79.13 in [2010 mm]
- Internal Width: 17.76 in [451 mm]
- Internal Depth:: 36 in [914.4 mm]
- Maximum Mounting Depth:: 36 in [914.4 mm]
- Industry Standards: EIA RS310-C
- Product Weight: 121.55 lb [55 kg]

