

45U 3300lb High Capacity 4 Post Open Server Equipment Rack - Flat Pack

StarTech ID: 4POSTRACKHD



This 45U 4 Post Open Frame Server Equipment Rack offers a solid, reliable solution for mounting servers, UPSs, and other heavy rack-mountable equipment.

Supporting a total weight capacity of up to 3300lbs (without casters) - nearly double the capacity of competitive models, this full size (45U) rack features an open frame design with heavy gauge mounting rails that ensure exceptional structural stability.

Built to meet EIA standards for 19in racks, the 4-post open frame rack is compatible with equipment and accessories from most popular manufacturers.

A durable, cost-effective server room storage solution, StarTech.com's DuraRak 45U 4 Post Open Frame Server Equipment Rack is backed by 2-year warranty.

Applications

- Ideal mounting option for heavy equipment like UPSs and storage servers in environments such as server farms, factory and other industrial applications
- Equipped to support servers, KVM switches, networking equipment and cabinet consoles
- Suitable for rack mount equipment where security at the rack level is not required

Features

- Fixed heavy duty rails with front/rear and side mounting options
- Easily route, manage and access your equipment cables without any obstruction
- Heavy-duty design supporting a maximum weight load of 3300 lb. (1493.21 kg.)with Pre-drilled holes allowing the rack to be secured directly to the floor for additional stability
- Open frame design with heavy gauge mounting rails provides exceptional structural stability
- Provides ample ventilation and unobstructed air flow keeping your rack mount equipment at room temperature
- Meets ANSI/EIA RS-310-D standards
- Package includes all necessary hardware to assemble the rack with a **free** pack of 50 cage screws and nuts for immediate hardware installation
- Flat-pack packaging for easier handling and reduced shipping expenses. Assembles in minutes.

Technical Specifications

Warranty	Lifetime
U Height	45U
Frame Type	Open Frame
Wallmountable	No
Front Door Type	Open
Industry Standards	EIA RS310-C
Fan(s)	No
Weight Capacity	3300 lb [1493.2 kg]
Color	Black
Internal Width	17.8 in [451 mm]
Internal Height	79.1 in [2010 mm]
Internal Depth	36 in [914.4 mm]
External Width	24 in [609 mm]
External Height	84.1 in [2135 mm]
External Depth	36 in [914.4 mm]
Product Weight	121.6 lb [55 kg]
Maximum Mounting Depth	36 in [914.4 mm]
Flat Pack	Yes
Shipping (Package) Weight	125.1 lb [56.6 kg]
Included in Package	1 - 4 Post Heavy Duty Rack Assembly Kit
Included in Package	1 - Pack of 50 Screws and Nuts
Included in Package	1 - Assembly instructions

Certifications, Reports and Compatibility

