

140m 50/125 Multimode LC-LC Fiber Cable (Special Order)

StarTech ID: 50FIBLCLC140



Your company's backbone is its Network. Without a stable, reliable network your company can't communicate. A lack of communication means a loss of revenue. What do you do now? Enter StarTech.com duplex 50/125 Multimode Fiber Optic cables. This product provides the necessary link between Fiber networking devices for high-speed, long-distance networks. Ideal for Gigabit networks, 50/125-micron cables offer nearly three times the bandwidth of 62.5/125-micron cables, so your data will be transferred at higher rates over longer distances.

Applications

- Broadband systems
- Ideal solution for data applications requiring high speed data transmission
- Telecommunication / Data communication
- Used by long distance networks with mission critical data

Features

- Connectors offer greater durability in resisting pulls, strains, and impacts during cable installation and maintenance
- Immune to electricity interference

Technical Specifications

Warranty	Lifetime
Fiber Size	50/125
Connector A	2 - Fiber Optic LC Male
Connector B	2 - Fiber Optic LC Male
Fiber Type	Multi Mode
Cable Type	: Duplex Multimode
Connector A	: LC (male)
Connector B	LC (male)
Fiber Size	: 50/125 micron
Color	Orange
Cable Length	459.1 ft [140 m]
Product Length	459.1 ft [140 m]
Shipping (Package) Weight	1.7 lb [0.8 kg]

Certifications, Reports and Compatibility

