

50m Multimode 50/125 Duplex Fiber Patch Cable LC - LC (Special Order)

StarTech ID: 50FIBLCLC50



This LC/LC Duplex 50/125 Multimode Fiber Patch Cable provides the necessary connection between fiber networking devices for high-speed, long distance networks.

Ensuring optimal data transfers and network stability, 50/125-micron cables offer nearly three times the bandwidth of 62.5/125-micron cables, so your data will be transferred at higher rates over longer distances.

Each Duplex 50/125 Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Applications

- Broadband systems
- Ideal solution for data applications requiring high speed data transmission
- Telecommunication / Data communication
- Used by long distance networks with mission critical data

Features

- Connectors offer greater durability in resisting pulls, strains, and impacts during cable installation and maintenance
- Immune to electricity interference

Technical Specifications

Warranty	Lifetime
Fiber Size	50/125
Connector A	2 - Fiber Optic LC Male
Connector B	2 - Fiber Optic LC Male
Fiber Type	Multi Mode
General Specifications	: 50/125 micron
General Specifications	: Duplex Multimode
General Specifications	: LC (male)
General Specifications	LC (male)
Color	Orange
Cable Length	164 ft [50 m]
Product Length	164 ft [50 m]
Shipping (Package) Weight	0.6 lb [0.3 kg]

Certifications, Reports and Compatibility

