

41U 36in Black Server Rack Cabinet

StarTech ID: 7236CABINET



This 41U 36in Black Server Rack Cabinet offers a lockable, dust-reduced environment for rackmount servers and network equipment.

With exterior dimensions of H 75.5in x W22in x D35.5in (cabinet only), this sturdy space-saving unit is made from extruded aluminum for an appealing appearance. A standard lockable smoked plexiglass (see-through) front door and solid aluminum rear door provide quick access to installed equipment.

The internal front and rear mounting rails are spaced to accept standard 19in rackmount devices and are completely depth adjustable as to be able to fit virtually any piece of equipment that is less than 33in deep. A standard roof-mounted triple motor AC fan unit and high-flow air filter below the rear door provide up to 300 CFM of bottom to top air flow through the cabinet, removing the heat produced by the enclosed equipment.

In addition to the standard equipment that are options on most other cabinets, the StarRack Cabinet also has a full complement of optional accessories like fixed shelving, storage drawers, keyboard drawers, front panel spacer plates, and slide-out shelves.

Features

- Also comes with front flip-up stabilizers, removable smoked acrylic front door with 2 keys, removable rear door and 50 Philips-head mounting screws
- Comes fully assembled
- Extruded aluminum construction provides rounded corners and edges for an attractive appearance
- Front and back doors are removable and can be switched to open left or right
- Fully forward/back adjustable mounting rails inside cabinet
- Includes (3) 5" ball bearing AC fans moving up to 300 CFM of air, air filter and adjustable levelers at each corner
- Many accessory options available like mounting shelves, keyboard drawers, storage drawers, sliding shelves, front blanking plates, etc.
- Rolling casters provide full mobility
- Three (3) roof-mounted fans exhaust up to 300 CFM of air

Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Key Lock: Yes
- Fans: 3 - 120 mm
- Carton Quantity: 1
- Industry Standards: EIA RS310-C
- U Height: 41
- Weight Capacity: 2210 lb [1000 kg]
- Shipping (Package) Weight: 232.05 lb [105 kg]
- Frame Type: : Steel
- Front Door Type: : Steel with Glass Window
- Back Door Type: : Solid Steel
- Side Panel Type: : Solid Steel
- Casters:: Included
- Noise Level: 39 dBa
- Input Voltage: 115 AC
- Input Current: 0.13/0.14 A
- External Height : 75.5 in [1917.7 mm]
- External Width : 22 in [558.8 mm]

- External Depth : 35.5 in [901.7 mm]
- Internal Height: 71.81 in [1824 mm]
- Internal Width: 19.02 in [483 mm]
- Internal Depth:: 31.4 in [797.56 mm]
- Height with Casters:: 75.59 in [1920 mm]
- Industry Standards: EIA RS310-C

