

41U 36in Black Server Rack Cabinet

StarTech ID: 7236CABINET



This 41U 36in Black Server Rack Cabinet offers a lockable, dust-reduced environment for rackmount servers and network equipment.

With exterior dimensions of H 75.5in x W22in x D35.5in (cabinet only), this sturdy space-saving unit is made from extruded aluminum for an appealing appearance. A standard lockable smoked plexiglass (see-through) front door and solid aluminum rear door provide quick access to installed equipment.

The internal front and rear mounting rails are spaced to accept standard 19in rackmount devices and are completely depth adjustable as to be able to fit virtually any piece of equipment that is less than 33in deep. A standard roof-mounted triple motor AC fan unit and high-flow air filter below the rear door provide up to 300 CFM of bottom to top air flow through the cabinet, removing the heat produced by the enclosed equipment.

In addition to the standard equipment that are options on most other cabinets, the StarRack Cabinet also has a full complement of optional accessories like fixed shelving, storage drawers, keyboard drawers, front panel spacer plates, and slide-out shelves.

Features

- Extruded aluminum construction provides rounded corners and edges for an attractive appearance
- Fully forward/back adjustable mounting rails inside cabinet
- Front and back doors are removable and can be switched to open left or right
- Rolling casters provide full mobility
- Three (3) roof-mounted fans exhaust up to 300 CFM of air
- Many accessory options available like mounting shelves, keyboard drawers, storage drawers, sliding shelves, front blanking plates, etc.
- Comes fully assembled
- Includes (3) 5" ball bearing AC fans moving up to 300 CFM of air, air filter and adjustable levelers at each corner
- Also comes with front flip-up stabilizers, removable smoked acrylic front door with 2 keys, removable rear door and 50 Philips-head mounting screws

Technical Specifications

Warranty	Lifetime
Casters	Included
U Height	41U
Frame Type	Enclosed Cabinet
Wallmountable	No
Front Door Type	Steel w/ Window
Side Panel Type	Solid Steel
Back Door Type	Solid Steel
Key Lock	Yes
Industry Standards	EIA RS310-C
Industry Standards	EIA RS310-C
Fan(s)	Yes
Fans	3 - 120 mm
Weight Capacity	2210 lb [1000 kg]
Air Flow Rate	82.8 CFM (each)
Noise Level	39 dBA
Color	Black
Internal Width	18.3 in [465 mm]
Internal Height	71.8 in [1824 mm]
Internal Depth	31.4 in [797.6 mm]
External Width	22 in [560 mm]
External Height	75.6 in [1920 mm]
External Depth	35.4 in [900 mm]
Height with Casters	78.6 in [1997 mm]
Input Voltage	115 AC
Input Current	0.13/0.14 A
Note	Includes 2 locking front casters, and 2 rear swivel casters
Flat Pack	No
Shipping (Package) Weight	232.1 lb [105 kg]
Included in Package	1 - H72"xW19"xD36" 41U Cabinet Equipment Rack
Included in Package	1 - Bag of screws, fasteners and keys

Certifications, Reports and Compatibility

