

## 12cm AC Fan Kit for Server Rack Cabinet

StarTech ID: ACFANKIT12



The ACFANKIT12 12cm AC Fan Kit for Server Racks and Cabinets can be installed in StarTech.com's Wall mountable Server Rack Cabinets (RK1219WALL and RK1219WALH), as well as many full sized racks from StarTech.com and other manufacturers.

This powerful, yet quiet ball bearing fan will help increase airflow and reduce heat build-up within the cabinet. Capable of moving 107 CFM of air through the rack, this AC powered fan kit is sure to prolong the life of your rackmount equipment.

Backed by a StarTech.com 2-year warranty.

### Applications

- Increase airflow, and reduce heat around rack mounted hardware

### Features

- Standard AC Power connection
- Removable 115V plug for use with direct current
- Solid metal frame and sturdy design

## Technical Specifications

Warranty	2 Years
Fan Bearing Type	Ball Bearing
Fan RPM	3050
Air Flow Rate	107 CFM
Noise Level	47.5 dBA
Color	Black
Enclosure Type	Aluminum
Product Length	4.7 in [120 mm]
Product Width	1.5 in [38 mm]
Product Height	4.7 in [120 mm]
Product Weight	19.4 oz [550 g]
Input Voltage	115 AC
Operating Temperature	-105/8/2012eg;C to 705/8/2012eg;C (145/8/2012eg;F to 1585/8/2012eg;F)
Shipping (Package) Weight	1.6 lb [0.7 kg]
Included in Package	1 - 120mm x 120mm x 38mm Fan
Included in Package	4 - #8 Zinc Plated Split Lock Washer
Included in Package	4 - 8-32 x 2" Phillips Pan Head Zinc Plated Machine Screw Bulk
Included in Package	4 - 8-32 Zinc Plated Machine Screw Nut
Included in Package	1 - AC Power Cord

## Certifications, Reports and Compatibility

