

## Adjustable Depth Fixed Server Rack Cabinet Shelf

StarTech ID: ADJSHELF



The ADJSHELF Adjustable Depth Fixed Server Rack Cabinet Shelf offers a simple way to effectively organize mission critical computer hardware in your server racks and cabinets.

Compatible with all 19in (wide) server racks/cabinets, the fixed rack shelf can be adjusted from 19in to 38in (depth) as necessary. A sturdy cold-rolled steel construction provides long term durability and enables a weight capacity of up to 175 lbs (80 kg).

Backed by a StarTech.com 2-year warranty.

### Applications

- For use with all 19" wide Server Racks and Cabinets
- Supply additional storage space for mission critical hardware.

### Features

- Low cost adjustable shelf for most 19 inch wide cabinets and racks
- adjustable mounting depth of 19" -38"
- Vented shelf plate to preserve airflow
- Weight capacity up to 175 lbs (80 kg)

## Technical Specifications

Warranty	2 Years
U Height	1U
Weight Capacity	176.8 lb [80 kg]
Color	Black
Internal Width	17.6 in [446 mm]
Internal Height	1.6 in [40 mm]
Internal Depth	27.6 in [700 mm]
External Width	18.9 in [480 mm]
External Height	1.6 in [40 mm]
Product Length	27.6 in [700 mm]
Product Width	17.5 in [445 mm]
Product Height	1.6 in [40 mm]
Product Weight	155.3 oz [4400 g]
Maximum Mounting Depth	38.3 in [974 mm]
Minimum Mounting Depth	19.5 in [495 mm]
<b>Note</b>	Depth adjustable from 19-38"
Shipping (Package) Weight	11.9 lb [5.4 kg]
Included in Package	1 - Slotted Fixed Shelf
Included in Package	2 - Front Mounting Bracket
Included in Package	2 - Rear Mounting Bracket
Included in Package	1 - Mounting Hardware

## Certifications, Reports and Compatibility

