

330 Watt Silent ATX12V PC Computer Power Supply with 120mm Fan
StarTech ID: ATXPOW330HS



This 330 Watt ATX12V power supply offers whisper-quiet performance and provides guaranteed compatibility with many 3GHz and faster Intel and AMD processors as well as a broad selection of eMachines and other Gateway systems.

The power supply features a TX3 fan sensor and 12cm dual ball-bearing fan that automatically adjusts speeds as you work, providing superior cooling for your entire system.

Backed by 2 year warranty, StarTech.com's 330 Watt ATX12V power supply is designed to provide dependable power for your hard working PC.

Features

- ATX version 2.03, ATX12V and Serial ATA 1.0 compliant
- High airflow 12cm dual ball bearing fan delivers efficient cooling for the entire system
- High quality connectors provide minimal resistance and enhanced electrical conductivity
- Includes power connectors for Serial ATA Devices
- Industry's leading safety approval ratings
- Premium EMI/RFI power filtration system provides low noise/ripple for super clean and stable power to all system components
- Provides a maximum output power of 330 watts
- Quad Protection Plus: Short Circuit Protection, Over Voltage Protection, Over Load Protection, Over Current Protection, and No Load Operation.

Technical Specifications

- Warranty: 2 Year warranty
- Air Flow Rate: 62.4
- Connector Types: 1 - ATX 20 pin Female
- Connector Types: 6 - LP4 Female
- Connector Types: 2 - SP4 Female
- Enclosure Type: Steel
- Fan Bearing Type: Ball Bearing
- Product Height: 3.35 in [8.5 cm]
- Input Current: 4 - 8
- Input Voltage: 240 AC
- Input Voltage: 120 AC
- Input Voltage Frequency: 50 - 60
- Product Length: 5.91 in [15 cm]
- MTBF: 100,000 Hrs
- Noise Level: 19 - 24
- Fans: 1 - 120 mm
- Current -12.0V (A): 0.8
- Current -5.0V (A): 0.5
- Current +12.0V1 (A): 15
- Current +3.3V (A): 28

- Current +5.0V (A): 35
- Current +5.0Vsb (A): 2.5
- Output Power: 330
- Carton Quantity: 10
- Shipping (Package) Weight: 4.35 lb [1.97 kg]
- Product Weight: 4.5 lb [2.03 kg]
- Product Width: 5.51 in [14 cm]

