

## 350 Watt Dual Fan ATX Replacement Computer PC Power Supply

*StarTech ID: ATXPOW350DF*



This 350 Watt ATX12V PC Power Supply is a reliable upgrade for Intel and AMD CPU-based systems, or replacement power supply for a broad selection of eMachines and other Gateway systems. To ensure ideal operating conditions, the power supply features two ball-bearing fans to help keep the PSU and surrounding area cool.

This high performance 350W PSU is constructed of high quality components and designed to provide a long-lasting, reliable power source for hard-working PCs.

## Applications

- Replacement upgrades for standard 250W, 300W & 350W ATX12V Power Supplies
- Replacement Power Supply for **Bestec ATX-300-12E**
- Compatible with following **eMachines A-Series Model:**  
A26EV17F
- Compatible with following **eMachines C-Series Models:**  
C1641, C1844, C1904, C2160, C2280, C2480, C2684, C2685, C2782, C2825
- Compatible with following **eMachines D-Series Models:**  
D2046, D2244, D2246, D2266, D2346, D2386, D2586, D2685
- Compatible with following **eMachines H-Series Models:**  
H2341, H2482, H2542, H2602, H2615, H2642, H2742, H2825, H2865
- Compatible with following **eMachines S-Series Models:**  
S1642, S1862, S1940, S2482, S2485
- Compatible with following **eMachines W-Series Models:**  
W1500, W1640, W1700, W1800, W2040, W2047, W2060, W2247, W2060, W2247, W2260, W2646,  
W2686, W2785, W2958, W4682, W4065
- Compatible with following **eMachines T-Series Models:**  
T1140, T1150, T1220, T1221, T1300, T1360, T1440, T1600, T1740, T1742, T1782, T1840, T1842, T1860,  
T1862, T1980, T2040, T2042, T2080, T2082, T2085
- **T-Series (cont'd):**  
T2200, T2200SE, T2240, T2245, T2260, T2341, T2385, T2460, T2482, T2484, T2542, T2596, T2605,  
T2615, T2625, T2642
- **More T-Series:**  
T2672, T2682, T2692, T2698, T2778, T2792, T2796, T2798, T2824, T2825, T2842, T2865, T2875, T2882,  
T2885, T2895, T3025, T3265, T4060, T4080, T4170, T4480, T4510, T4511, T4697, T6000
- Compatible with following **Gateway Models:**  
DX100, B330

## Features

- Provides a maximum output power of 350 watts
- Ball Bearing temperature controlled smart fan provides increased reliability, air flow and longer life
- TX3 Fan sensor connector allows the fan speed and operation status to be monitored thru the system motherboard monitor
- High quality connectors provide minimal resistance and enhanced electric conductivity
- Additional power connectors are provided to connect several drives
- Premium EMI/RFI power filtration system provides low noise/ripple for super clean and stable power to all system components
- ATX version 2.03 and ATX12V complaint
- Enclosure is constructed with an attractive gold color casing
- Quad Protection Plus: Short Circuit Protection, Over Voltage Protection, Over Load Protection, Over Current Protection, and No Load Operation.

## Technical Specifications

|                           |   |
|---------------------------|---|
| Warranty                  | 3 Years   |
| Fans                      | 2 - 80 mm                                       |
| Fan Bearing Type          | Ball Bearing                                    |
| Output Connectors         | 1 - ATX 12V P4 Power (4 pin; v 2.x) Male        |
| Output Connectors         | 1 - ATX Power (20 pin; v 1.x) Male              |
| Output Connectors         | 2 - SP4 (4 pin; Small Drive Power) Female       |
| Output Connectors         | 6 - LP4 (4 pin; Molex Large Drive Power) Female |
| Air Flow Rate             | 39.8 CFM  |
| Noise Level               | 32.6 dBA  |
| Power Factor Correction   | No  |
| MTBF                      | 100,000 Hours                                   |
| Product Length            | 5.9 in [15 cm]                                  |
| Product Width             | 5.9 in [14.9 cm]                                |
| Product Height            | 3.3 in [8.5 cm]                                 |
| Product Weight            | 4.5 lb [2 kg]                                   |
| Max Inrush Current        | 50  |
| Current -12.0V (A)        | 0.8   |
| Current -5.0V (A)         | 0.5   |
| Current +12.0V1 (A)       | 15  |
| Current +3.3V (A)         | 28  |
| Current +5.0V (A)         | 35  |
| Current +5.0Vsb (A)       | 2.5   |
| Input Voltage             | 115 ~ 230 AC                                    |
| Shipping (Package) Weight | 4.7 lb [2.1 kg]                                 |
| Included in Package       | 1 - 350W ATX12V P4 Power Supply - Dual Fan      |
| Included in Package       | 1 - Power Cord                                  |
| Included in Package       | 1 - Instructional Manual                        |

## Certifications, Reports and Compatibility



