

10 Piece Bulk 300 Watt ATX Replacement Computer PC Power Supply

StarTech ID: ATXPOWER300B



A reliable upgrade or replacement power supply for desktop PCs.

This StarTech.com power supply offers an upgrade or replacement to a variety of Intel or AMD-based ATX desktop computer systems. Compliant with the industry standard ATX specification and using the standard ATX form-factor, this power supply (PSU) can be used as a replacement in a variety of popular OEM desktop systems.

Conforming to ATX revision 2.03, this power supply features a 20-pin ATX power connector and 6-pin AUX power connector, for support for older, legacy computer systems, as well as some newer, low powered systems with it's ATX12V connector. High quality components and a built in 80mm cooling fan lend to a durable and reliable power supply, while being backed by StarTech.com's 2 year warranty and free lifetime technical support.

Applications and Solutions

- b>T-Series (cont'd):

T2200, T2200SE, T2240, T2245, T2260, T2341, T2385, T2460, T2482, T2484, T2542, T2596, T2605, T2615, T2625, T2642

- Compatible with following **eMachines A-Series Model:**

A26EV17F

- Compatible with following **eMachines C-Series Models:**C1641, C1844, C1904, C2160, C2280, C2480, C2684, C2685, C2782, C2825

- Compatible with following **eMachines D-Series Models:**

D2046, D2244, D2246, D2266, D2346, D2386, D2586, D2685

- Compatible with following **eMachines H-Series Models:**

H2341, H2482, H2542, H2602, H2615, H2642, H2742, H2825, H2865

- Compatible with following **eMachines S-Series Models:**S1642, S1862, S1940, S2482, S2485

- Compatible with following **eMachines T-Series Models:**T1140, T1150, T1220, T1221, T1300, T1360, T1440, T1600, T1740, T1742, T1782, T1840, T1842, T1860, T1862, T1980, T2040, T2042, T2080, T2082, T2085

- Compatible with following **eMachines W-Series Models:**W1500, W1640, W1700, W1800, W2040, W2047, W2060, W2247, W2060, W2247, W2260, W2646, W2686, W2785, W2958, W3080, W4682, W4065

- Compatible with following **Gateway Models:**

DX100, B330

- More **T-Series:**T2672, T2682, T2692, T2698, T2778, T2792, T2796, T2798, T2824, T2825, T2842, T2865, T2875, T2882, T2885, T2895, T3025, T3265, T4060, T4080, T4170, T4480, T4510, T4511, T4697, T6000

- Replacement for standard 250W & 300W ATX12V Power Supplies

- Replacement Power Supply for **Bestec ATX-300-12E**

Features

- 2 years warranty
- ATX version 2.03 and ATX12V compliant
- High quality connectors provide minimal resistance and enhanced electric conductivity
- High-Flow fan provides efficient cooling for the system and power supply
- Long-life transformer and built-in short-circuit protection
- Premium EMI/RFI power filtration system provides low noise/ripple for super clean and stable power to all system components
- Provides a maximum output power of 300 watts
- Quad Protection Plus: Short Circuit Protection, Over Voltage Protection, Over Load Protection, Over Current Protection, and No Load Operation.
- The temperature controlled smart fan cools your entire system while the EMI/RFI power filter reduces noise/ripple

Technical Specifications

- Warranty: 2 Year warranty
- Connector Types: 1 - AUX Power 6-pin Female
- Fans: 1 - 80 mm
- Current -12.0V (A): 0.8
- Current -5.0V (A): 0.3
- Current +12.0V1 (A): 15
- Current +3.3V (A): 28
- Current +5.0V (A): 30
- Current +5.0Vsb (A): 2.0
- Package Quantity:: 10
- Power Factor Correction: No
- Carton Quantity: 10
- Shipping (Package) Weight: 39.12 lb [17.7 kg]
- Output Power: 300W
- Weight: Carton 41.36 lbs
- Dimensions: 5.9 x 3.35 x 5.87 inches (150 x 85 x 149mm)
- MTBF: 40,000 Hours
- Connectors: 6 x 4-pin-LP4-female
 - 2 x small-internal-power

- 1 x 20-pin-ATX-motherboard-adapter
- AC INPUT: (Voltage 115V~ Current 8A)(Voltage 230V~ Current 4A)
- Frequency: 50~60Hz
- DC OUTPUT: +3.3V(15A)
 - +5V(29A)
 - +12V(11.5A)
 - -5V(0.5A)
 - -12V(0.5A)
 - +5V(1.5A)