

10 Piece Bulk 300 Watt ATX Replacement Computer PC Power Supply

StarTech ID: ATXPOWER300B



A reliable upgrade or replacement power supply for desktop PCs.

This StarTech.com power supply offers an upgrade or replacement to a variety of Intel or AMD-based ATX desktop computer systems. Compliant with the industry standard ATX specification and using the standard ATX form-factor, this power supply (PSU) can be used as a replacement in a variety of popular OEM desktop systems.

Conforming to ATX revision 2.03, this power supply features a 20-pin ATX power connector and 6-pin AUX power connector, for support for older, legacy computer systems, as well as some newer, low powered systems with it's ATX12V connector. High quality components and a built in 80mm cooling fan lend to a durable and reliable power supply, while being backed by StarTech.com's 2 year warranty and free lifetime technical support.

Applications

- Replacement for standard 250W & 300W ATX12V Power Supplies
- Replacement Power Supply for **Bestec ATX-300-12E**
- Compatible with following **eMachines A-Series Model:**
A26EV17F
- Compatible with following **eMachines C-Series Models:**
C1641, C1844, C1904, C2160, C2280, C2480, C2684, C2685, C2782, C2825
- Compatible with following **eMachines D-Series Models:**
D2046, D2244, D2246, D2266, D2346, D2386, D2586, D2685
- Compatible with following **eMachines H-Series Models:**
H2341, H2482, H2542, H2602, H2615, H2642, H2742, H2825, H2865
- Compatible with following **eMachines S-Series Models:**
S1642, S1862, S1940, S2482, S2485
- Compatible with following **eMachines W-Series Models:**
W1500, W1640, W1700, W1800, W2040, W2047, W2060, W2247, W2060, W2247, W2260, W2646,
W2686, W2785, W2958, W3080, W4682, W4065
- Compatible with following **eMachines T-Series Models:**
T1140, T1150, T1220, T1221, T1300, T1360, T1440, T1600, T1740, T1742, T1782, T1840, T1842, T1860,
T1862, T1980, T2040, T2042, T2080, T2082, T2085
- b>T-Series (cont'd):
T2200, T2200SE, T2240, T2245, T2260, T2341, T2385, T2460, T2482, T2484, T2542, T2596, T2605,
T2615, T2625, T2642
- More **T-Series:**
T2672, T2682, T2692, T2698, T2778, T2792, T2796, T2798, T2824, T2825, T2842, T2865, T2875, T2882,
T2885, T2895, T3025, T3265, T4060, T4080, T4170, T4480, T4510, T4511, T4697, T6000
- Compatible with following **Gateway Models:**
DX100, B330

Features

- Provides a maximum output power of 300 watts
- High-Flow fan provides efficient cooling for the system and power supply
- High quality connectors provide minimal resistance and enhanced electric conductivity
- Premium EMI/RFI power filtration system provides low noise/ripple for super clean and stable power to all system components
- ATX version 2.03 and ATX12V compliant
- 2 years warranty
- Quad Protection Plus: Short Circuit Protection, Over Voltage Protection, Over Load Protection, Over Current Protection, and No Load Operation.
- Long-life transformer and built-in short-circuit protection
- The temperature controlled smart fan cools your entire system while the EMI/RFI power filter reduces noise/ripple

Technical Specifications

Warranty	2 Years
Fans	1 - 80 mm
Output Connectors	1 - ATX AUX Power (6 pin; v 1.x) Female
Output Connectors	1 - ATX Power (20 pin; v 1.x) Female
Output Connectors	2 - SP4 (4 pin; Small Drive Power) Female
Output Connectors	6 - LP4 (4 pin; Molex Large Drive Power) Female
Output Power	300W
Power Factor Correction	No
MTBF	40,000 Hours
Product Length	5.9 in [150 mm]
Product Width	5.9 in [149 mm]
Product Height	3.3 in [85 mm]
Input Voltage Frequency	50Hz ~ 60Hz
Current -12.0V (A)	0.8
Current -5.0V (A)	0.3
Current +12.0V1 (A)	15
Current +3.3V (A)	28
Current +5.0V (A)	30
Current +5.0Vsb (A)	2.0
Input Voltage	115 ~ 230 AC
Input Current	8A ~ 4A
Package Quantity	10
Shipping (Package) Weight	39.1 lb [17.7 kg]
Included in Package	10 - 10 Pcs. ATXPOWER300 Power Supplies
Included in Package	10 - 10 Power Cords