

## 300 Watt ATX12V 2.01 Dell Replacement PC Computer Power Supply

StarTech ID: ATXPW300DELL



This 300 Watt ATX12V 2.01 Dell Replacement Power Supply is a reliable upgrade or replacement for many compatible Dell computers (see compatible models below). It offers dual 12V power rails to deliver stable power to demanding components, and both 20 and 24-pin ATX motherboard power connectors and a generous number of component connectors to ensure broad system compatibility.

Constructed of high quality components and designed to provide a long-lasting, durable power source for hard-working PCs, the 300 Watt ATX12V 2.01 Dell PC Replacement Power Supply is backed by StarTech.com's 2 year warranty and free lifetime technical support.

**The 300 Watt ATX12V 2.01 Dell PC Power Supply is compatible with standard ATX style versions of following:**

**Dimension Series Models:** 2100 / 4100 / B1000R / L Series / V350 / V400 / XPS B Series / XPS Dxxx / XPS Mxxx / XPS P133c MT / XPS Pro 180n / XPS Rxxx / XPS Txxx

**Optiplex Series Models:** GN / GN+ / G1 / GX1 / GX1p / GX100 / GX110 / GX115 / GX300 / Gxa / Gxi

**Power Edge Series Models:** 2100 / 2200

**Precision Workstation Series Models:** 210 / 400

### Applications and Solutions

- Designed as ideal replacement or upgraded power supply for compatible proprietary Dell systems (see list in Overview)

## Features

- 20/24 split motherboard connector
- 80mm fan provides efficient cooling for the system and the power supply
- ATX12V version 2.01 compliant
- EMI/RFI power filtration system provides low noise/ripple for super clean and stable power to all system components
- High quality connectors provide minimal resistance and enhanced electric conductivity
- SATA connectors for SATA Hard Drive support

## Technical Specifications

- Warranty: 2 Year warranty
- Air Flow Rate: 32.3
- Connector Types: 1 - Split 24/20 pin ATX Motherboard
- Connector Types: 4 - LP4 Female Large Internal Power
- Connector Types: 2 - SATA Power Female
- Connector Types: 1 - SP4 Female Small Internal Power
- Connector Types: 1 - AUX Power 6-pin Female
- Fan Bearing Type: Sleeve Bearing
- Product Height: 3.39 in [86 mm]
- Input Current: 8 ~ 4
- Input Voltage: 115 ~ 230
- Input Voltage Frequency: 50~60 Hz
- Product Length: 5.51 in [140 mm]
- MTBF: 100000
- Fans: 1 - 80 mm
- Operating Temperature: 0° ~ 50°
- Current -12.0V (A): 0.8A
- Current +12.0V1 (A): 8A
- Current +12.0V2 (A): 14A
- Current +3.3V (A): 20A
- Current +5.0V (A): 20A
- Current +5.0Vsb (A): 2.0A
- Output Power: 300

- PCI Express Power Connector: 1 - Yes
- Power Factor Correction: No
- Carton Quantity: 6
- Storage Temperature: -20° ~ 80°
- Shipping (Package) Weight: 4.4 lb [1.99 kg]
- Product Weight: 4.11 lb [1.86 kg]
- Product Width: 5.91 in [150 mm]
- General Specifications: Zinc-plated casing

