

2U Rack Blank Panel for 19in Server Racks and Cabinets

StarTech ID: BLANKB2



The BLANKB2 2U Rack Blank Panel for 19in Server Racks and Cabinets is designed to EIA RS-310-C specifications and fits all 19" standard server racks and cabinets.

Ideal for improving airflow within the rack by covering the unused spaces, the filler panel/blank panel is constructed of cold-rolled steel and features a black powder coated finish that matches most industry standard black server cabinets and racks.

Applications

- Filling in the spaces when no other rack mounted equipment is needed
- Assist with directing air flow

Features

- SPCC Cold Rolled Steel, 1.2mm thick
- Powder black coloring to match most rack and cabinets

Technical Specifications

Warranty	Lifetime
U Height	2U
Frame Type	Steel
Industry Standards	EIA RS310-C
Color	Black
External Width	19 in [482.6 mm]
External Height	3.5 in [88 mm]
External Depth	0.5 in [13 mm]
Product Weight	18.4 oz [520.4 g]
Shipping (Package) Weight	1.3 lb [0.6 kg]
Included in Package	1 - 2 U Blanking Plate
Included in Package	1 - Package of M6 Screws and Cage nuts (4 sets)

Certifications, Reports and Compatibility

