

4 Port 10/100 Cable/DSL Broadband Router

StarTech ID: BR4100DC



Set up a high-speed network with only one Internet connection! Save the cost of extra connections, modems and switches! The BR4100DC DSL/Cable Router connects to your broadband modem or Ethernet backbone, allowing you to connect up to 253 users via four 10/100 Mbits/sec ports. A web based user interface and Quick Setup Wizard walks you through installation and configuration and makes ongoing remote management simple and straightforward. Plus, to protect your network, the router comes with a built-in, configurable firewall that blocks hacker intrusion. And for extra security, the router uses NAT (Network Address Translation) to keep your private IP addresses hidden from unauthorized users. Advanced features like Virtual Server, Remote Access, DMZ, Access Control, and Address Mapping let you configure the router to meet the exact needs of your network solution. Backed by StarTech.com's 2-year warranty and FREE lifetime tech support.

Applications

- Allows multiple users to share existing Internet resources via a single cable or xDSL modem connection
- Perfect for home or office use
- Ideal for multiple workgroup environments with shared internet access

Features

- NAT firewall blocks unauthorized users from accessing your private IP addresses
- Remote management function allows network configuration and management from anywhere, over the Internet
- Intuitive Quick Install Wizard for easy setup and configuration
- LED indicators continuously show operating status
- Virtual server capability enables incoming access to specified FTP, e-mail and other servers
- Supports IP functions including PPTP, PPPoE, DHCP and NAT
- Supports VPN – PPTP/L2TP/IPSec pass-through
- Advanced functions include DMZ, and Access Control
- Allows monitoring of Security Log, DHCP PC Client Log, Internet Connection, System Information and Device Status
- Compact wall-mountable design saves desktop space
- 2-year warranty and FREE LIFETIME tech support

Technical Specifications

Warranty	2 Years
Ports	4
Industry Standards	IEEE802.3
Industry Standards	IEEE802.3u
External Ports	5 - RJ-45 Female
Maximum Data Transfer Rate	100000000 Mbits/Sec
Remote Management Ability	Yes
Full Duplex Support	Yes
Security Features	MAC Address Filtering
Security Features	NAT Firewall
Security Features	Virtual DMZ
General Specifications	
General Specifications	1.1 x 7.3 x 3.9
General Specifications	10 Mbits/sec
General Specifications	20 Mbits/sec
General Specifications	253
General Specifications	30 x 187 x 100
General Specifications	4
General Specifications	4 x 10/100 Mbits/sec RJ45 Base-T Port
General Specifications	AC Adapter 12V
General Specifications	Blue
General Specifications	Connection status @ 100 Mbits/sec
General Specifications	Connection status and activity status
General Specifications	FCC class B, CE Mark & C-Tick
General Specifications	IEEE802.3 & IEEE802.3u
General Specifications	Internet network connection status @ 100 Mbits/sec
General Specifications	Internet network connection status and activity status
General Specifications	PC or MAC with RJ-45 Ethernet Connection
General Specifications	Plastic
General Specifications	Shows router's power supply status
Supported Protocols	DHCP
Supported Protocols	ICMP
Supported Protocols	MS-CHAP
Supported Protocols	NAT/PAT

Supported Protocols	PAP/CHAP
Supported Protocols	PPPoE
Supported Protocols	PPTP
Supported Protocols	RIP1/2
Supported Protocols	TCP/IP
Supported Protocols	UDP
Color	Blue
Enclosure Type	Plastic
Product Length	7.4 in [187 mm]
Product Width	3.9 in [100 mm]
Product Height	1.2 in [30 mm]
LED Indicators	1 - LAN 10 / 100 Mbit connection status
LED Indicators	1 - LAN Link and Activity
LED Indicators	1 - Power
LED Indicators	1 - WAN 10 / 100 Mbit connection status
LED Indicators	1 - WAN Link and Activity
Power Adapter Included	Yes
Input Voltage	12 DC
Shipping (Package) Weight	1.8 lb [0.8 kg]

Certifications, Reports and Compatibility

