

1ft Blue Shielded Cat6a Molded STP Patch Cable

StarTech ID: C6ASPAT1BL



This high quality (blue) 1ft Cat 6a cable (STP) ensures dependable Ethernet connectivity, supporting 10 Gigabit performance up to 500 MHz - double that of standard Category 6 cable and five times the bandwidth offered by Cat5 - an excellent choice for Power over Ethernet (PoE) applications.

Plus, Cat 6a cables are backward-compatible with Cat5e and Cat6 cables, ensuring versatile network connection options.

High Quality Cat 6a Cables

All of our Cat 6a cables are constructed of high quality 26 AWG shielded copper pairs to protect against noise and EMI/RFI interference, ensuring that our Cat6a cables are more than suitable for 10GBase-T Ethernet networks and Power over Ethernet applications.

Broad Industry Compliance

StarTech.com Cat 6a patch cables provide end-to-end solutions that are tested for compliance with all TIA/ETL-568-B2.10 Category 6, UL® 444 and ROHS 2002/95/EC specifications.

Lifetime Warranty

Our Cat 6a STP patch cables are backed by Lifetime Warranty, guaranteeing durable, long term performance.

Technical Specifications

- Warranty: Lifetime warranty
- Color: Blue
- Connector Types: 1 - RJ45 Male
- Connector Types: 1 - RJ45 Male
- Carton Quantity: 250
- Shipping (Package) Weight: 0.07 lb [0.03 kg]
- Network Cable Type: Molded
- Cable Shield Type: Aluminum-polyester foil
- Cable Jacket Type: PVC - Polyvinyl Chloride
- Cable Length: 1 ft [0.3 m]
- Wire Gauge: 26 AWG
- Cable Rating: CAT6a - 10Gbit/s

