

## 1 ft Cat 6a Blue Shielded Molded 10 Gigabit RJ45 STP Cat6a Patch Cable

StarTech ID: C6ASPAT1BL



This high quality (blue) 1ft Cat 6a cable (STP) ensures dependable Ethernet connectivity, supporting 10 Gigabit performance up to 500 MHz - double that of standard Category 6 cable and five times the bandwidth offered by Cat5 - an excellent choice for Power over Ethernet (PoE) applications.

Plus, Cat 6a cables are backward-compatible with Cat5e and Cat6 cables, ensuring versatile network connection options.

### High Quality Cat 6a Cables

All of our Cat 6a cables are constructed of high quality 26 AWG shielded copper pairs to protect against noise and EMI/RFI interference, ensuring that our Cat6a cables are more than suitable for 10GBase-T Ethernet networks and Power over Ethernet applications.

### Broad Industry Compliance

StarTech.com Cat 6a patch cables provide end-to-end solutions that are tested for compliance with all TIA/ETL-568-B2.10 Category 6, UL® 444 and ROHS 2002/95/EC specifications.

### Lifetime Warranty

Our Cat 6a STP patch cables are backed by Lifetime Warranty, guaranteeing durable, long term performance.

## Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-polyester foil
Cable Type	Molded
Connector A	1 - RJ-45 Male
Connector B	1 - RJ-45 Male
Cable Rating	CAT6a - 10Gbit/s
Color	Blue
Wire Gauge	26 AWG
Cable Length	1 ft [0.3 m]
Product Length	1 ft [0.3 m]
Shipping (Package) Weight	0.1 lb [0 kg]
Included in Package	1 - 1ft Blue Shielded Cat6a Molded STP Patch Cable

## Certifications, Reports and Compatibility

