

3 ft Cat 6 Yellow Molded Gigabit Crossover RJ45 UTP Cat6 Patch Cable

StarTech ID: C6CROSS3YL



StarTech.com's Cat 6 UTP Crossover Patch Cables offer reliable Ethernet connections. This 3ft cable is ETL verified to meet or exceed all Category 6 performance standards, and features a durable yellow jacket that simplifies departmental color coding while providing rugged flexibility for network connections.

Featuring top quality construction (100% copper conductors, 23 Gauge Wire and 50 Micron gold connectors), our Cat6 Crossover cables are built to last and backed by lifetime warranty.

Applications

- Use crossover cable to directly connect two computers without the need for a hub
- Connect two Ethernet hubs/switches together with crossover cable
- Category 6 cables support gigabit networks

Features

- StarTech.com Category 6 crossover cables are manufactured to meet or exceed CAT6 specifications
- Molded strain relief and stranded wires for added flexibility and durability
- Colored Hoods for departmental color coding and easy identification
- Molded ends with top-quality connectors

Technical Specifications

Warranty	Lifetime
Number of Conductors	4 pair UTP
Cable Type	Crossover Molded
Wiring Standard	TIA/EIA-568-B.1-2001 T568B
Connector A	1 - RJ-45 Male
Connector B	1 - RJ-45 Male
Cable Rating	CAT6 - 500 MHz
Color	Yellow
Wire Gauge	24 AWG
Cable Length	3 ft [0.9 m]
Product Length	3 ft [0.9 m]
Shipping (Package) Weight	0.1 lb [0.1 kg]
Included in Package	1 - 3 ft. Yellow Category 6 Crossover Cable

Certifications, Reports and Compatibility

