

10U 19in Wall Mounted Server Rack Cabinet

StarTech ID: CAB1019WALL



This 10U Wall Mounted Server Rack Cabinet can be mounted to most wall materials, allowing you to securely position your rackmount equipment exactly as needed.

The server rack offers 10U of storage space and is designed to accommodate 19in (wide) equipment. To ensure a cool operating environment for your networking equipment, the server rack includes a 5in roof-mounted fan (85 CFM) and vented side panels - not only helping to keep temperatures down, but keep dust out of the rack.

To secure network equipment from tampering, the cabinet features a lockable, smoked acrylic front door, that can be removed entirely or installed to open to the left or right as needed.

Applications and Solutions

- Audio/Visual control centers
- Data centers
- Industrial control centers
- Telecommunication closets

Features

- Comes fully assembled
- Front door is removable and can be switched to open left or right
- Fully adjustable mounting rails inside cabinet
- Includes (1) 5" (12cm) Ball bearing AC fan moving up to 85 CFM of air, lockable & removable smoked acrylic front door with 2 keys
- One roof-mounted fan exhaust up to 85 CFM of air
- Stylish enclosure is designed for durability and easy accessibility

Technical Specifications

- Warranty: Lifetime warranty
- Color: Beige
- Key Lock: Yes
- Weight Capacity: 132.6 lb [60 kg]
- Frame Type: : Steel
- Front Door Type: : Steel with Glass Window
- Industry Standards: EIA RS310-C
- Fans: 1 - 5 Inch
- Noise Level: 36
- Air Flow Rate: 85
- Input Voltage: 115 AC
- Input Current: 180 mA
- External Height : 20 in [508 mm]
- External Width : 22 in [558.8 mm]
- External Depth : 24 in [609.6 mm]
- Internal Height: 18 in [457.2 mm]
- Internal Width: 19 in [482.6 mm]
- Internal Depth:: 22.7 in [576.58 mm]
- U Height: 10
- Product Weight: 48.58 lb [21.98 kg]
- Maximum Mounting Depth:: 17.75 in [450.85 mm]
- Carton Quantity: 1
- Shipping (Package) Weight: 51.23 lb [23.18 kg]

