

## Refurbished 10U 19in Wall Mounted Server Rack Cabinet

StarTech ID: CAB1019WALLR



This refurbished 10U Wall Mounted Server Rack Cabinet can be mounted to most wall materials, allowing you to securely position your rackmount equipment exactly as needed.

The server rack offers 10U of storage space and is designed to accommodate 19in (wide) equipment. To ensure a cool operating environment for your networking equipment, the server rack includes a 5in roof-mounted fan (85 CFM) and vented side panels - not only helping to keep temperatures down, but keep dust out of the rack.

To secure network equipment from tampering, the cabinet features a lockable, smoked acrylic front door, that can be removed entirely or installed to open to the left or right as needed.

Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty,.

### Applications

- Mounting standard 19 in. networking equipment in exposed or insecure locations
- Data centers
- Industrial control centers
- Telecommunication closets
- Audio/Visual control centers

## Features

- Comes fully assembled
- Front door is removable and can be switched to open left or right
- Fully adjustable mounting rails inside cabinet
- Includes (1) 5" (12cm) Ball bearing AC fan moving up to 85 CFM of air, lockable & removable smoked acrylic front door with 2 keys
- One roof-mounted fan exhaust up to 85 CFM of air
- Stylish enclosure is designed for durability and easy accessibility

## Technical Specifications

|                           |                                   |
|---------------------------|-----------------------------------|
| Warranty                  | 0 Years                           |
| U Height                  | 10U                               |
| Frame Type                | Enclosed Cabinet                  |
| Wallmountable             | Yes                               |
| Front Door Type           | Steel w/ Window                   |
| Side Panel Type           | Solid Steel                       |
| Key Lock                  | Yes                               |
| Industry Standards        | EIA RS310-C                       |
| Fan(s)                    | Yes                               |
| Weight Capacity           | 132.6 lb [60 kg]                  |
| Air Flow Rate             | 85 CFM                            |
| Color                     | Beige                             |
| Internal Width            | 18.3 in [465 mm]                  |
| Internal Height           | 17.6 in [448 mm]                  |
| Internal Depth            | 22.7 in [576.6 mm]                |
| External Width            | 22 in [560 mm]                    |
| External Height           | 20 in [508 mm]                    |
| External Depth            | 23.6 in [600 mm]                  |
| Product Weight            | 48.6 lb [22 kg]                   |
| Maximum Mounting Depth    | 19 in [482.6 mm]                  |
| Input Voltage             | 115 AC                            |
| Input Current             | 180 mA                            |
| Flat Pack                 | No                                |
| Shipping (Package) Weight | 23180                             |
| Included in Package       | 1 - Cabinet                       |
| Included in Package       | 1 - Mounting Bracket              |
| Included in Package       | 1 - Set of Keys                   |
| Included in Package       | 1 - Package of Cab Screw Cage Nut |

## Certifications, Reports and Compatibility

