

16 Port USB PS/2 KVM Switch Modules for 1UCABCONS/17/19

StarTech ID: CAB1631HD



This 16 Port USB+PS/2 KVM Switch Module is designed for use with StarTech.com's 1UCABCONS (1UCABCONS, 1UCABCONS17, 1UCABCONS19) 1U Modular LCD KVM Rack Console, allowing the console to control both USB and PS/2 controlled computers/servers.

The USB+PS/2 KVM Switch Module is 1U in height, allowing you to neatly position it behind a rackmounted console to provide additional functionality.

A scalable and versatile KVM solution, the USB+PS/2 module can be cascaded with multiple KVM switches, delivering control of up to 136 computers from this single module.

Featuring a rugged and durable design, the USB+PS/2 module for StarTech.com's 1UCABCONS series is backed by our 3-year warranty.

Applications and Solutions

- Co-location/ISP computer control
- Datacenter computer control
- Manufacturing line computer control
- PC test/burn-in computer control
- Server farms

Features

- Auto Scan Mode lets you switch between computers for easy monitoring
- Compact 1U rack height takes up very little cabinet or rack space
- Compatible with PC, Mac and Sun servers and systems
- DDC2B compatible
- Each computer name can be defined via the OSD menu
- Hot-pluggable feature allows computers to be added or removed without shutting down
- Login authentication restricts access to authorized users
- No software or drivers required
- Operating system independent
- Plug and Play compliant
- Supports IntelliMouse (Pro)
- Supports PCs with USB or PS/2 keyboard and mouse connectors
- Universal 16 port KVM switch Module controls up to 16 computers directly and up to 136 computers by cascading 8 additional KVM switches
- Uses StarTech.com tangle-free KVM cables

Technical Specifications

- Warranty: 3 Year warranty
- Color: Black
- Enclosure Type: Steel
- Audio Support: No
- Cascadable: Yes
- Dual Display Support: No
- DVI Support: No
- Supported Platforms: Both USB and PS/2
- KVM IP Control: No
- Number of KVM Ports: 16
- Rack-Mountable: Yes
- KVM TFT: None
- Product Length: 7.09 in [180 mm]
- Maximum Cascaded Computers: 136
- Maximum Number of Computers: 16
- Maximum Analog Resolutions: 1920 x 1440 pixels
- Maximum Number of Users: 1
- OSD & Hotkey Support: Yes
- Power Adapter - Amperage: 0.6A
- Power Adapter - DC Voltage: 9V DC
- Power Consumption: 0.6W
- Carton Quantity: 5
- U Height: 1
- Shipping (Package) Weight: 5.02 lb [2.27 kg]
- Product Width: 17.17 in [436 mm]
- Computer Port Connectors: 16 x HD-15 (Female)
- Console Port Connector: 1 x PS/2 Keyboard 6-pin Mini-Din (Female)1 x PS/2 Mouse 6-pin Mini-Din (Female)1 x HD-15 (Female)
 - Centronics Connector: 1 x 36 pin Centronics connector (Connects 8 port KVM module to 1UCABCONS or IUCABCONS17)
 - Channel Selection: Hotkeys
 - Auto Scan Interval: 3,8,15 & 30 seconds
 - Login Password: 4 character/computer

- OSD Support: Yes
- Computer Name Entry: 14 Characters
- Cable Length: 100ft for Console Connection 100ft for PS/2 Computers 15ft for USB Computers
- Enclosure: Metal
- Dimensions: 17.2 Inches x 1.7 Inches x 7.0 Inches (436 x 180 x 44 mm)
- Safety Standards: FCC & CE

