

## 2 User 8 Port PS/2 Standalone KVM Switch or 1UCABCONS Series Module

StarTech ID: CAB832DS



This dual user shared 8-Port KVM Switch can be used as a standalone switch or as a module combined with our DuraView 1UCABCONS series (1UCABCONS, 1UCABCONS17, 1UCABCONS19) 1U Folding Rackmount LCD Consoles.

Adding versatility and convenience, this switch/module offers two user console access, allowing multiple computers to be controlled from two consoles/control points as opposed to just one.

**Note:** This product is designed to work in a "cascaded" configuration as a master KVM with non dual-user slave units attached.

### Features

- Ability to assign computers with unique and meaningful names
- Supports both PS/2 and serial mice, including the Microsoft Intellimouse (Pro) and scroll mice
- LCD panel on 1UCABCONS supports VGA resolution up to 1024x768 without any degradation
- Cascade configuration expands system ability allowing user to select computers connected to master and cascaded slave
- Password security locks computer(s) from unauthorized access

**Technical Specifications**

Warranty	3 Years
Audio	No
KVM Ports	8
PC Interface	PS/2
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	Yes
U Height	1U
Daisy-Chain	Yes
Console Interface(s)	2 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	4 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	16 - PS/2 (6 pin; Mini-DIN) Female
Host Connectors	8 - VGA (15 pin; High Density D-Sub) Male
Other Interface(s)	1 - Centronics (50 pin) Female
Other Interface(s)	1 - Mini-DIN (8 pin) Female
Brightness	
Contrast Ratio	
Response Time	
Viewing Angle	
DVI Support	No
IP Control	No
Maximum Cable Length	1200 in [3048 cm]
Maximum Analog Resolutions	1920 x 1440 pixels
Maximum Number of Users	2
General Specifications	10 x DB15, 20 x PS/2
General Specifications	100ft (30m) at console, 100ft at PC ports
General Specifications	1920x1440, DDC2B compatible
General Specifications	2 x Cabinet 19" 1U Rack mount brackets with screws
General Specifications	2 x PS/2 Female to DB9 Female serial mice adapters
General Specifications	3, 8, 15 and 30 seconds
General Specifications	FCC (Part 15)
General Specifications	OS independent, transparent to all applications
General Specifications	Plug and play
General Specifications	Yes, keyboard and mouse

Product Length	7.1 in [180 mm]
Color	Black
Enclosure Type	Steel
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Input Current	1.8A
Output Voltage	12 DC
Output Current	4A
Center Tip Polarity	Positive
Plug Type	M
Shipping (Package) Weight	5 lb [2.3 kg]
Included in Package	1 - 1UCABCONS 2 User Shared 8 Pt KVM Module
Included in Package	2 - Mouse Adapters
Included in Package	1 - Bag of Screws
Included in Package	1 - Instruction Sheet
Included in Package	1 - StarTech Manual

**Certifications, Reports and Compatibility**

