

## 1U 15in Folding Rackmount LCD Console

StarTech ID: CABCONS1



Instead of wasting your valuable cabinet space with a bulky monitor, keyboard and mouse set up, get efficient with the StarTech.com CABCONS1, a 1U cabinet console for 19" racks. A complete space-saving cabinet solution, this eye-catching 15-inch active-matrix LCD monitor, 105-key low profile keyboard, and touchpad fold down into just 1U of space. When you don't need the CABCONS1, you can close the console like a laptop and slide it into the cabinet and out of your way.

The Cabinet Command Console is able to work with virtually any existing KVM switch and any standard rack or cabinet that is 30" or greater in depth; all mounting hardware is included.

### Applications and Solutions

- Centralized control of dozens of PCs and servers if used with optional KVM modules
- Improving the internal space efficiency of existing cabinets
- Managing cabinet mounted servers

## Features

- All mounting hardware is included
- Console can be connected to any KVM switch
- High resolution 15" Active Matrix color TFT LCD monitor
- Laptop design with an integrated keyboard and touchpad mouse makes it comfortable to use
- Steel construction makes the product rugged and durable
- Supports resolution up to 1024x768 Pixels
- The compact and efficient way to control multiple computers in a 19" by 36" deep Rack Cabinet

## Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Connector Types: 2 - 6 DIN Female
- Connector Types: 1 - High Density DB15 Male
- Enclosure Type: Steel
- Audio Support: No
- Cascadable: Yes
- Dual Display Support: No
- DVI Support: No
- Supported Platforms: PS/2
- KVM IP Control: No
- Number of KVM Ports: 1
- Rack-Mountable: Yes
- KVM TFT: None
- Product Length: 4.49 in [114 mm]
- Maximum Analog Resolutions: 1024 x 768 pixels
- Maximum Number of Users: 1
- Power Adapter Included: Yes
- Power Adapter - Amperage: 4A
- Power Adapter - DC Voltage: 12V
- Center Tip Polarity: Positive
- Power Consumption: 3.75W

- Carton Quantity: 1
- U Height: 1
- Shipping (Package) Weight: 31.38 lb [14.2 kg]
- Product Weight: 576.45 oz [16330 g]
- Product Width: 15.91 in [404 mm]
- LCD: 15 Inches Active matrix TFT LCD Panel
- VGA Bandwidth: 300MHz
- Auto Scan interval: 3, 8, 15 & 30 Seconds
- Computer Connectors:
- Keyboard: 1 x PS/2
- Mouse: 1 x PS/2
- Monitor: 1 x HDB-15
- LED Indicators:
- Computer Indicator: N/A
- Local Console: N/A
- Remote Console: N/A
- Keyboard Status: 1 x Num Lock, 1 x Caps Lock & 1 x Scroll Lock
- LCD Power Switch: Indicates LCD power status
- Panel Control Buttons:
- Selection Pad: N/A
- LCD Panel Menu: up or down buttons for OSD Menu selection
- LCD Panel Adjustment: + or – for LCD Panel Settings
- Console Dimensions:
- Length: 4.5 Inches (114 millimeters)
- Width: 15.9 Inches (404 millimeters)
- Height: 1.6 Inches (40 millimeters)
- Rack/Cabinet Depth Requirement: 30 in. (minimum)

