

## 1U 15in Folding Rackmount LCD Console

StarTech ID: CABCONS1



Instead of wasting your valuable cabinet space with a bulky monitor, keyboard and mouse set up, get efficient with the StarTech.com CABCONS1, a 1U cabinet console for 19" racks. A complete space-saving cabinet solution, this eye-catching 15-inch active-matrix LCD monitor, 105-key low profile keyboard, and touchpad fold down into just 1U of space. When you don't need the CABCONS1, you can close the console like a laptop and slide it into the cabinet and out of your way.

The Cabinet Command Console is able to work with virtually any existing KVM switch and any standard rack or cabinet that is 30" or greater in depth; all mounting hardware is included.

### Applications

- Managing cabinet mounted servers
- Improving the internal space efficiency of existing cabinets
- Centralized control of dozens of PCs and servers if used with optional KVM modules

### Features

- The compact and efficient way to control multiple computers in a 19" by 36" deep Rack Cabinet
- Laptop design with an integrated keyboard and touchpad mouse makes it comfortable to use
- High resolution 15" Active Matrix color TFT LCD monitor
- Supports resolution up to 1024x768 Pixels
- Console can be connected to any KVM switch
- Steel construction makes the product rugged and durable
- All mounting hardware is included

**Technical Specifications**

Warranty	2 Years
Audio	No
KVM Ports	1
PC Interface	PS/2
Multi-Monitor	No
Rack-Mountable	Yes
U Height	1U
Daisy-Chain	Yes
DVI Support	No
IP Control	No
Maximum Analog Resolutions	1024 x 768 pixels
Maximum Number of Users	1
General Specifications	
General Specifications	+ or – for LCD Panel Settings
General Specifications	1 x HDB-15
General Specifications	1 x Num Lock, 1 x Caps Lock & 1 x Scroll Lock
General Specifications	1 x PS/2
General Specifications	1.6 Inches (40 millimeters)
General Specifications	15 Inches Active matrix TFT LCD Panel
General Specifications	15.9 Inches (404 millimeters)
General Specifications	3, 8, 15 & 30 Seconds
General Specifications	30 in. (minimum)
General Specifications	300MHz
General Specifications	4.5 Inches (114 millimeters)
General Specifications	Indicates LCD power status
General Specifications	N/A
General Specifications	up or down buttons for OSD Menu selection
Color	Black
Enclosure Type	Steel
Product Length	4.5 in [114 mm]
Product Width	15.9 in [404 mm]
Product Weight	576.4 oz [16330 g]
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC

Input Current	1.8A
Output Voltage	12 DC
Output Current	4A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption	3.75W
Shipping (Package) Weight	31.4 lb [14.2 kg]
Connector Type(s)	1 - VGA (15 pin; High Density D-Sub) Male
Connector Type(s)	2 - PS/2 (6 pin; Mini-DIN) Female

**Certifications, Reports and Compatibility**

