

4 Port CardBus RS232 Serial Laptop PC Adapter Card - 16950

StarTech ID: CB4S950



The CB4S950 4 Port CardBus RS232 Serial Laptop PC Adapter Card (16950 UART) adds four RS232 serial ports to a notebook computer, letting you connect your mobile computer to serial peripheral devices.

The 4-port Cardbus RS232 adapter supports data transfer rates of up to 921 Kbps, and features a high performance 16950 UART chipset, ensuring flawless connectivity with your serial peripherals. The included breakout cable separates the four ports, avoiding crowded connections.

Backed by a StarTech.com lifetime Warranty and free, lifetime technical support.

Applications

- Connect up to 4 RS-232 serial devices to a CardBus slot on your notebook
- Works with serial modems, POS devices, PDAs, digital cameras, printers, ISDN terminal adapters, and more

Features

- Offers 4 DB9 RS-232 ports to connect multiple devices to a notebook PC
- High Performance 16C950 UART with maximum data transfer rate up to 921.6 kbps
- 128-byte deep FIFO data buffer

Technical Specifications

Warranty	Lifetime
Ports	4
Bus Type	CardBus (PCMCIA)
Port Style	Dongle (Included)
Chipset ID	PLX/Oxford - OX16PCI954
Connector Type(s)	1 - PC Card (Type II; Cardbus)
Connector Type(s)	4 - DB-9 (9 pin; D-Sub) Male
Maximum Data Transfer Rate	921.6 Kbps
Serial Protocol	RS-232
OS Compatibility	Windows® 98SE/ME/2000/XP/Vista
Operating Temperature	0 to 55°C
Storage Temperature	-40 to 75°C
Shipping (Package) Weight	0.7 lb [0.3 kg]
Included in Package	1 - Cardbus Serial Card
Included in Package	1 - 4 Port DB9 Break-out Cable
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

