

2 Port CardBus eSATA Laptop Controller Adapter Card

StarTech ID: CBESAT2



This 2 port CardBus eSATA Adapter offers a cost-effective external storage solution that allows eSATA laptop connections to external SATA devices.

The eSATA laptop (PCMCIA) adapter is ideal for making routine backups or dumping data to SATA hard drives.

The eSATA CardBus Adapter presents a convenient way to protect your valuable data, with full external SATA data transfer speeds of up to 150MBps.

Applications and Solutions

- Enables effortless transport of high-capacity and high-performance Serial ATA hard drives
- Gives you 2 eSATA ports from your laptop
- With a quicker maximum data transfer rate (150MBps), it makes it easier to do data off loads

Features

- Compatible with 32-bit CardBus
- Data transfer rates up to 150MBps
- Plug and Play installation gets you up and running instantly
- Provides you with a faster transfer rate opposed to USB and FireWire
- Supports two high-speed eSATA channels for SATA/II device connections
- Two external Serial ATA (eSATA) ports

Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: CardBus (PCMCIA)
- Chipset ID: Silicon Image - Sil3512
- Product Height: 0.59 in [15 mm]
- Humidity: 0 to 85% RH
- Product Length: 4.53 in [115 mm]
- Maximum Data Transfer Rate: 150Mbps
- Number of Ports: 2
- Operating Temperature: 0°C to 70°C (32°F to 158°F)
- Carton Quantity: 50
- Storage Temperature: -10°C to 85°C (14°F to 185°F)
- Shipping (Package) Weight: 0.75 lb [0.34 kg]
- Product Weight: 1.51 oz [42.9 g]
- Microsoft WHQL Certified: Yes
- Product Width: 2.17 in [55 mm]
- OS Compatibility: Windows 98SE/ ME/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, and Linux

