

5m DisplayPort® Cable with Latches - M/M

StarTech ID: DISPL5M



The DISPL5M 5-meter DisplayPort® Cable supports a maximum bandwidth of 10.8 Gbps, and is capable of providing higher performance than either HDMI® or dual link DVI, while supporting next generation multimedia applications with a maximum resolution capability of up to WQXGA (2560×1600).

The cable features latching connectors, with support for two-way display connectivity and optional audio support.

This 5-meter DisplayPort cable is both HDCP and DPCP capable, ensuring that digitally protected content is displayed properly on the connected display.

Applications

- Connecting a DisplayPort® display to a PC or other DisplayPort source

Features

- Molded latching connectors with strain relief
- Designed and manufactured to DisplayPort® standards
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP

Technical Specifications

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Connector A	1 - DisplayPort (20 pin) Male
Connector B	1 - DisplayPort (20 pin) Male
Color	Black
Connector Style	Latching
Wire Gauge	28 AWG
Cable Length	16.4 ft [5 m]
Cable OD	0.3 in [7.3 mm]
Product Weight	11.3 oz [320 g]
Package Quantity	1
Shipping (Package) Weight	11.3 oz [320 g]
Included in Package	1 - 5m Latching DisplayPort Cable

Certifications, Reports and Compatibility

