

## 25 ft DisplayPort Cable with Latches - M/M

StarTech ID: *DISPLPORT25L*



This high quality 25ft DisplayPort cable provides a connection of up to 25ft between a DisplayPort source and a DisplayPort display, with no loss of signal quality - more than double the typical DisplayPort connection distance limitation (16ft).

Featuring 26 gauge (AWG) pure copper wire, the cable includes aluminium and mylar shielding to help eliminate EMI and RFI interference and maintain signal integrity without any degradation of quality.

Supporting a maximum bandwidth of 10.8Gbps and display resolutions up to 2560x1600 (WQXGA), DisplayPort is capable of providing higher performance than either HDMI or dual link DVI. Each cable features small, USB-sized latching connectors with support for two-way display connectivity and optional audio support. Plus, DisplayPort cables feature a unique micro-packet architecture that supports new display features as the DisplayPort standard is further developed.

This 25ft DisplayPort cable is HDCP and DPCP compliant, ensuring that digitally protected content is displayed properly on the connected display.

### Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Shipping (Package) Weight: 1.19 lb [0.54 kg]

- Length: 25 ft
- Cable Length: 25 ft [7.62 m]
- Cable Jacket Type: PVC - Polyvinyl Chloride
- Cable Shield Type: Aluminum-Mylar Foil with Braid
- Wire Gauge: 26 AWG
- Connector Plating: Nickel
- Carton Quantity: 25
- Packaging Style: Bagged

