

## 35 ft DisplayPort® Cable with Latches - M/M

StarTech ID: *DISPLPORT35L*



The DISPLPORT35L 35-foot DisplayPort® cable provides a connection of up to 35ft between a DisplayPort source and a DisplayPort display, with no loss of signal quality – more than double the typical DisplayPort connection distance limitation of 16ft. Its 26 gauge (AWG) pure copper wire, and Aluminum and Mylar shielding helps to eliminate EMI and RFI interference. Delivering a maximum bandwidth of 10.8 Gbps, the DISPLPORT35L is capable of providing higher performance than either HDMI® or dual link DVI and supporting next generation multimedia applications with a maximum resolution capability of up to WQXGA (2560×1600).

The DisplayPort cable's small, USB-sized latching connectors support two-way display connectivity and optional audio support.

The DISPLPORT35L DisplayPort cable is both HDCP and DPCP capable, ensuring that digitally protected content is displayed properly on the connected display.

### Applications

- Connecting a DisplayPort® display to a PC or alternative DisplayPort source

### Features

- Molded latching connectors with strain relief
- Supports the DPCP (DisplayPort® Content Protection) standard in addition to HDCP
- Designed and manufactured to DisplayPort standards

## Technical Specifications

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Connector A	1 - DisplayPort (20 pin) Male
Connector B	1 - DisplayPort (20 pin) Male
Color	Black
Connector Style	Latching
Wire Gauge	26 AWG
Cable Length	35 ft [10.7 m]
Cable OD	0 in [0.3 mm]
Product Weight	1.9 lb [0.9 kg]
Shipping (Package) Weight	1.9 lb [0.9 kg]
Included in Package	1 - 35 ft DisplayPort® Cable with Latches - M/M

## Certifications, Reports and Compatibility

