

6 ft DisplayPort® Cable with Latches - M/M

StarTech ID: DISPLPORT6L



The DISPLPORT6L 6-foot DisplayPort® Cable supports a maximum bandwidth of 10.8 Gbps, and is capable of providing higher performance than either HDMI® or dual link DVI and supporting next generation multimedia applications with a maximum resolution capability of up to WQXGA (2560×1600).

The DisplayPort cable's small, USB-sized latching connectors support two-way display connectivity and optional audio support.

Featuring 30 gauge (AWG) pure copper wire, the cable includes Aluminum and Mylar shielding to help eliminate EMI and RFI interference and maintain signal integrity without any degradation of quality.

The DISPLPORT6L DisplayPort cable is both HDCP and DPCP capable, ensuring that digitally protected content is displayed properly on the connected display.

Applications

- Connecting a DisplayPort® display to a PC or alternative DisplayPort source

Features

- Molded latching connectors with strain relief
- Supports the DPCP (DisplayPort® Content Protection) standard in addition to HDCP
- Designed and manufactured to DisplayPort standards

Technical Specifications

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Connector A	1 - DisplayPort (20 pin) Male
Connector B	1 - DisplayPort (20 pin) Male
Color	Black
Connector Style	Latching
Wire Gauge	30 AWG
Cable Length	6 ft [1.8 m]
Cable OD	0.3 in [6.5 mm]
Product Weight	0.6 lb [0.3 kg]
Shipping (Package) Weight	0.6 lb [0.3 kg]
Included in Package	1 - 6 ft DisplayPort® Cable with Latches - M/M

Certifications, Reports and Compatibility

