

3.5in IDE Hard Drive Mobile Rack for 5.25in Bay

StarTech ID: DRW113ATA



StarTech.com's DRW113ATA removable hard drive enclosure offers a cost-effective way to quickly insert or remove ATA hard drives from any PC with an available 5.25-inch drive bay without opening the computer. It is an ideal solution for high-speed back-ups of critical files, moving large files from one computer to another, and for running multiple operating systems on the same PC.

While providing security and minimizing downtime, the DRW113ATA features reliable shock absorbers and a sturdy aluminum caddy that helps limit physical damages to the enclosed hard drive during transport.

Included with the DRW113ATA is our exclusive Swap Manager software for Windows that allows you to hot-swap the removable drive without the need to power down the computer.

Applications

- Removable drive drawers can be used in homes, at work, offices, schools and in large enterprises
- Fast and easy way to make backup copies of your files, applications, company's critical data and for transporting databases and other large files from one location to another
- For use in servers and storage subsystems
- Perfect for mission critical control computers where downtime must be minimized

Features

- Easy to install and use
- Shock absorbers protect the hard drive
- Two front mounted ball bearing cooling fans keep the drive cool
- Lock controlled drive power prevents hard drive damage from accidental removal
- Power and activity lights indicate drive status
- Plastic bay and aluminum caddy enclosure for light weight and maximum durability
- With the included Swap Manager for Windows Software, the user can safely stop Windows from accessing the drive drawer, allowing the drive to be removed and replaced while the system is running.
- Supports hard drive ATA66/ATA100 & ATA133 with data transfer rate up to 133 MBytes/Sec

Technical Specifications

Warranty	2 Years
Key Lock	Yes
Fans	2 - 40 mm
Connector Type(s)	1 - IDE (40 Pin; EIDE/PATA) Female
Connector Type(s)	1 - IDE (40 Pin; EIDE/PATA) Male
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Female
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Male
General Specifications	1.45 lbs (0.66 kg)
General Specifications	40 Pin Header Female, 4 Pin LP4 Female
General Specifications	40 Pin Header Male, 4 Pin LP4 Male
General Specifications	8.625 x 5.75 x 1.61 Inches (220 x 148 x 41 mm)
General Specifications	Any PC or Mac with an IDE Hard Drive interface and an available 5.25 inch drive bay
General Specifications	Two front-mounted 4cm ball bearing fans
General Specifications	Unit is model specific and is not meant for use with different models of drive drawer unless otherwise stated
General Specifications	Yellow - Drive Activity, Green - Drive Power
Color	Beige
Enclosure Type	Aluminum
Product Length	8.7 in [220 mm]
Product Width	5.8 in [148 mm]
Product Height	1.6 in [41 mm]
Product Weight	23.3 oz [660 g]
LED Indicators	1 - Activity
LED Indicators	1 - Power
Shipping (Package) Weight	1.7 lb [0.8 kg]

Certifications, Reports and Compatibility

