

Black 3.5in IDE Hard Drive Mobile Rack for 5.25in Bay 2x fan

StarTech ID: DRW113ATABK



This high quality Removable ATA Hard Drive Drawer/Mobile Rack delivers a convenient ATA storage solution, allowing you to quickly swap ATA66/ATA100 and ATA133 hard drives in and out of a computer without having to open the computer case.

Simply install the (included) drive bay into a 5.25in drive bay on the host computer, then mount a 3.5in ATA HDD in the (removable) caddy. Connecting the ATA hard drive to the computer is as easy as inserting the caddy into the drive bay, which can be locked to prevent unauthorized removal of the installed ATA drive.

A practical, time-saving storage solution, the drive drawer/mobile rack features front panel LED indicators that continuously display the operating status of the installed drive.

The drive caddy features dual ball-bearing fans that help keep the enclosed drive cool, in turn helping to optimize operation while preserving drive lifespan. To prevent damage to the hard drive(s) while being transferred in and out of the computer, the drive caddy features shock absorbers and rubber cushioning that help limit vibration/shock to the drive.

A dependable, long-lasting storage solution, the drive drawer features highly durable construction, with a 3K insertion rating and is backed by StarTech.com's 2-year warranty.

Applications

- Medium duty model made out of Aluminum and plastic is ideal for use in homes, offices, schools and government institutions
- Can be conveniently used as a mobile back up system
- Fast and easy way to make backup copies of your files, applications, company's critical data and for transporting databases and other large files from one location to another
- For use in servers and storage subsystems
- Perfect for mission critical control computers where downtime must be minimized

Features

- Secure and affordable solution to store and transfer data
- Two Ball-bearing fans maintains optimum cooling and increased air flow
- Bay is built with a key lock mechanism to prevent the hard drive from being accidentally removed while in operation
- LED indicators continuously show operating status of the drive drawer
- The caddy is constructed with aluminum for maximum durability
- Supports hard drive ATA66/ATA100 & ATA133 with data transfer rate up to 133 MBytes/Sec
- Swap Manager Software allows the hard drive to be removed or replaced while the system is running

Technical Specifications

Warranty	2 Years
Key Lock	Yes
Fans	2 - 40 mm
Connector Type(s)	1 - IDE (40 Pin; EIDE/PATA) Female
Connector Type(s)	1 - IDE (40 Pin; EIDE/PATA) Male
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Female
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Male
Certifications	CE
Cooling Fan	Ball-Bearing Fan
CPU Compatibility	PC or MAC with a 5.25 Inch Drive Bay
Drive Activity	Yellow
Drive Drawer Bay	Plastic
Drive Drawer Dimensions	
Drive Drawer Enclosure	Aluminum
Drive Power	Green
Enclosure Color	Black
External Connector	
Fan Dimensions	
Fan Enclosure	Plastic
HD Compatibility	All 3.5 Inch IDE Hard Drives
Header	40 Pin Female
Header	40 Pin Male
Inches	1.57x1.57x0.39
Inches	8.6 x 5.75 x 1.61
Internal Connector	
LED Indicators	
LP4	4 Pin Female
LP4	4 Pin Male
Millimeters	220 x 148 x 41
Millimeters	40x40x10
Note	Unit is model specific and is not meant for use with different models of drive drawer unless otherwise stated
Weight (w/o drive)	1.15 lbs (0.53 kg)

Color	Black
Enclosure Type	Aluminum
Product Length	8.7 in [220 mm]
Product Width	5.8 in [148 mm]
Product Height	1.6 in [41 mm]
Product Weight	23.3 oz [660 g]
LED Indicators	1 - Activity
LED Indicators	1 - Power
Shipping (Package) Weight	1.7 lb [0.8 kg]

Certifications, Reports and Compatibility

