

## **Professional 5.25in Aluminum ATA Hard Drive Mobile Rack w/ 2x 40mm Fan**

*StarTech ID: DRW115ATABK*



This high quality Removable ATA Hard Drive Drawer/Mobile Rack delivers a convenient ATA storage solution, allowing you to quickly swap ATA66/ATA100 and ATA133 hard drives in and out of a computer without having to open the computer case.

Simply install the (included) drive bay into a 5.25in drive bay on the host computer, then mount a 3.5in ATA HDD in the (removable) caddy. Connecting the ATA hard drive to the computer is as easy as inserting the caddy into the drive bay, which can be locked to prevent unauthorized removal of the installed ATA drive.

A practical, time-saving storage solution, the drive drawer/mobile rack features front panel LED indicators that continuously display the operating status of the installed drive.

The drive caddy features dual ball-bearing fans that help keep the enclosed drive cool, in turn helping to optimize operation while preserving drive lifespan. To prevent damage to the hard drive(s) while being transferred in and out of the computer, the drive caddy features shock absorbers and rubber cushioning that help limit vibration/shock to the drive.

A dependable, long-lasting storage solution, the drive drawer features highly durable construction, with a 7K insertion rating and is backed by StarTech.com's 3 year warranty.

## **Applications and Solutions**

- Can be conveniently used as a mobile back up system
- For use in servers and storage subsystems
- Heavy duty model made out of aluminum is ideal for use in offices, enterprises, workstations, universities, government organizations or other environments with heavy work loads and usage
- Perfect for mission critical control computers where downtime must be minimized

## Features

- 4 LED indicators continuously show operating status of the drive drawer
- Caddy is built with a key lock mechanism to prevent the hard drive from being accidentally removed while in operation
- Can be mounted from the side or the bottom
- Supports hard drive ATA66/ATA100 & ATA133 with data transfer rate up to 133 MBytes/s
- Swap Manager Software allows the hard drive to be removed or replaced while the system is running
- The frame and caddy is constructed with aluminium for maximum durability
- Two ball-bearing fans maintain optimum cooling and increased air flow

## Technical Specifications

- Warranty: 3 Year warranty
- Color: Black
- Connector Types: 1 - IDC 40 Female
- Connector Types: 1 - IDC 40 Male
- Connector Types: 1 - LP4 Female
- Connector Types: 1 - LP4 Male
- Enclosure Type: Aluminum
- Product Height: 41
- Hot Swap Capability: Yes
- Key Lock: Yes
- LED Indicators: 1 - Power
- LED Indicators: 1 - Activity
- LED Indicators: 1 - Fan Failure
- LED Indicators: 1 - Temperature Warning
- Product Length: 236
- Fans: 2 - 40 mm
- Carton Quantity: 20
- Shock Protection: Yes
- Shipping (Package) Weight: 2.43 lb [1.1 kg]
- Product Weight: 980
- Product Width: 146
- HD Compatibility: All 3.5 Inch IDE Hard Drives

- CPU Compatibility: PC or MAC with a 5.25 Inch Drive Bay
- Weight (w/o drive): 2.15 lbs (0.98 kg)
- Internal Connectors:
  - Header: 40 Pin Female
  - LP4: 4 Pin Female
- External Connectors:
  - Header: 40 Pin Male
  - LP4: 4 Pin Male
- Drive Drawer Dimensions:
  - Inches: 9.25 x 5.75 x 1.61
  - Millimeters: 236 x 148 x 41
- LED Indicators:
  - Drive Activity: Yellow
  - Drive Power: Green
  - Fan Status: Red
  - Temperature: Normal - Green & Overheat - Red
- Cooling Fan: 2 Ball-Bearing Fans
- Fan Enclosure: Plastic
- Enclosure Color: Black
- Drive Drawer Enclosure: Aluminum
- Fan Dimensions:
  - Inches: 1.57x1.57x0.39
  - Millimeters: 40x40x10
- Certifications: CE
- Note: Unit is model specific and is not meant for use with different models of drive drawer unless otherwise stated

